




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART#	COLOR	DESCRIPTION	WEIGHT*
CJS5E88TGY CJS5E88TGRDY CJS5E88TGBUY CJS5E88TGGRY CJS5E88TGVLY CJS5E88TGWHY CJS5E88TGYLY	BLACK RED BLUE GREEN VIOLET WHITE YELLOW	8 POSITION, 8 WIRE SHIELDED MODULE WITH INTEGRAL SHIELD. WIRE CAP LABEL IS COLOR CODED FOR T568A AND T568B WIRING SCHEMES.	3.715 LB/100 PCS (1685g/100 PCS)

*WEIGHT IS APPROXIMATE

NOTES:

1. RED WIRE CAP DESIGNATES CATEGORY 5E PERFORMANCE.
2. MATERIAL:
MODULE HOUSING-ABS
SHIELD-TIN PLATED OVER PHOS. BRONZE
WIRE CAP/CLIP - ZINC AND PC
3. ALL TX5e,6 AND 6A 8 POSITION, 8 WIRE JACK MODULES ARE UNIVERSAL IN DESIGN. THEY ACCEPT SIX AND EIGHT POSITION MODULAR PLUGS WITHOUT DAMAGE.
4. DIMENSIONS IN PARENTHESES ARE IN METRIC.
5. .187" x .010" GROUNDING TAB PROVIDED AS OPTIONAL CONDUCTIVE PATH FOR GROUNDING.



PART NUMBER		CJS5E88TG**Y	
TITLE		TX5E SHIELDED JACK MODULE	
		CUSTOMER DRAWING	
ITEM REVISION NAME		M02479NR/06	PANDUIT
DATASET FILE NAME		M02479NR_DC356/06C	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL: SEE NOTE 2	
.X ± .XX ± .03 (.8)		.XXX ± .010 (.3) ANGLES ±	DRAWING NUMBER: 02479-356
THIRD ANGLE PROJECTION			
DRAWN BY AFW	DATE 3-11-06	CHK CEF	SCALE FULL
SHT 1 OF 1		A	

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
8	4-26-18	BJN	BSN	TMBA	UPDATED WEIGHT ALIGNED METRIC DIMENSIONAL EQUIVALENTS	02479-356
7	4-12-18	BJN	MDJR	TMBA	ADDED WHITE TO COLOR OPTIONS	02479-356
6	2-15-17	ROJC	NAGL	TMBA	MODEL REVISION UPDATED REMOVED PREVIOUS REVISIONS FOR CLARITY	02479-356

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[CJS5E88TGBUY](#) [CJS5E88TGGRY](#) [CJS5E88TGYLY](#) [CJS5E88TGVLY](#) [CJS5E88TGRDY](#)