

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	STUD SIZE	DIMENSIONS - in [mm]				
		A ± .03 [0,8]	W ± .01 [0,3]	C ± .02 [0,5]	M ± .03 [0,8]	H ± .01 [0,3]
P2-10R	#10	1.46 [37,1]	.68 [17,3]	.58 [14,7]	1.12 [28,5]	.20 [5,1]
P2-14R	1/4"	1.46 [37,1]	.68 [17,3]	.58 [14,7]	1.12 [28,5]	.27 [6,9]
P2-56R	5/16"	1.46 [37,1]	.68 [17,3]	.58 [14,7]	1.12 [28,5]	.33 [8,4]
P2-38R	3/8"	1.46 [37,1]	.68 [17,3]	.58 [14,7]	1.12 [28,5]	.39 [9,9]
P2-12R *	1/2"	1.55 [39,4]	.86 [21,8]	.58 [14,7]	1.12 [28,5]	.52 [13,2]


*P2-12R NOT CSA CERTIFIED

NOTES:

- UL LISTED AND CSA CERTIFIED FOR:
A. #2 AWG STRANDED COPPER WIRE
B. 302°F (150°C) MAX OPERATING TEMP
C. 2000 VOLTS MAX
- SEE WWW.PANDUIT.COM FOR PACKAGE QUANTITIES
- MATERIAL:
A. STAMPING - .060" [1,52] THK COPPER, TIN PLATED
- DIMENSIONS IN BRACKETS ARE IN MILLIMETERS
- WIRE STRIP LENGTH: $7/16" \begin{smallmatrix} +1/32 \\ -0 \end{smallmatrix} [11,1mm \begin{smallmatrix} +0,8 \\ -0 \end{smallmatrix}]$

UL & CSA TOOLS (DIES)


CT-1701 (P2)
CT-2600 (CD-2600-P2)



LISTED
587H
E52164



CERTIFIED
LR31212

TITLE					
#2 BARREL NON-INSULATED RING TONGUE					
CUSTOMER DRAWING					
ITEM REVISION NAME			PANDUIT		
N41212BB/08					
DATASET FILE NAME			N41212BB/08		
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]			MATERIAL:		
.X ± .XX ±			.XXX ± ANGLES ±		
			THIRD ANGLE PROJECTION		
DRAWN BY			DRAWING NUMBER:		
DAW			A41212		
DATE		CHK	SCALE	SIZE	
		RLS	NONE	A	
SHT 1 OF 1					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[P2-10R-T](#) [P2-10R-X](#) [P2-38R-T](#) [P2-12R-X](#)