


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

TWIST TIE



IDENTIFICATION LABEL

TANGLE-FREE LATCH

MODULAR PLUG

STRAIN RELIEF BOOT

SHIELD

PLUG POSITION 1

NOTES:

- **1. SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS.
2. SEE CATALOG FOR A COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. TERMINATED WITH (8 POSITION) SHIELDED MODULAR PLUGS AT BOTH ENDS PER T568B.
4. CONSTRUCTED WITH 26 AWG STRANDED CAT 6A FULLY SHIELDED TWISTED PAIR TYPE CMX OUTDOOR-CMR SF/UTP PATCH CABLE.
5. CABLE JACKET DIAMETER IS 0.29 IN (7.37MM) NOMINAL.

TABLE 1
T568B WIRING SCHEME

PLUG POSITION	CABLE WIRE
1	WHITE/ORANGE
2	ORANGE
3	WHITE/GREEN
4	BLUE
5	WHITE/BLUE
6	GREEN
7	WHITE/BROWN
8	BROWN

TABLE 2
CABLE COLOR OPTIONS

CABLE COLORS	** = COLOR
TEAL	TL
BLACK	BL

SEE SHEET 2 FOR PATCH CORD
LENGTHS AND PART NUMBERS

PART NUMBER

ISTPH6X**M**, SEE TABLE 3

TITLE

INDUSTRIAL ETHERNET CAT6A SHIELDED PATCH CORD
(600V RATED) WITH RJ45 CONNECTIVITY


CUSTOMER DRAWING

ITEM REVISION NAME

00173EAA/00

DATASET FILE NAME

00173EAA_DC/00A



THIRD ANGLE
PROJECTION

MATERIAL

SEE NOTES

DRAWING NUMBER

00173EAA_DC

PANDUIT

DRAWN BY

JBO

DATE

8/22/18

CHK

MGH

SCALE

NONE

SHEET 1 OF 2

SIZE


A

00A	8/22/18	JBO	MGH	EOS	INITIAL RELEASE	00173EAA_DC
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

INDUSTRIAL ETHERNET CAT6A SHIELDED PATCH CORD
(600V RATED) WITH RJ45 CONNECTIVITY

TABLE 3 PANDUIT PART NUMBERS	
PART NUMBER	MIN. CABLE LENGTH
ISTPH6X0.3M**	0.3 METERS
ISTPH6X0.6M**	0.6 METERS
ISTPH6X1M**	1 METER
ISTPH6X1.5M**	1.5 METER
ISTPH6X2M**	2 METERS
ISTPH6X2.5M**	2.5 METERS
ISTPH6X3M**	3 METERS
ISTPH6X3.5M**	3.5 METERS
ISTPH6X4M**	4 METERS
ISTPH6X4.5M**	4.5 METERS
ISTPH6X5M**	5 METERS
ISTPH6X7M**	7 METERS
ISTPH6X10M**	10 METERS
ISTPH6X15M**	15 METERS
ISTPH6X20M**	20 METERS



CROSS-SECTIONAL VIEW OF CABLE

PART NUMBER		ISTPH6X**M**, SEE TABLE 3	
TITLE		INDUSTRIAL ETHERNET CAT6A SHIELDED PATCH CORD (600V RATED) WITH RJ45 CONNECTIVITY	
ITEM REVISION NAME		CUSTOMER DRAWING	
DATASET FILE NAME		00173EAA/00	
THIRD ANGLE PROJECTION		PANDUIT	
MATERIAL		DRAWING NUMBER	
SEE NOTES		00173EAA_DC	
DRAWN BY	DATE	CHK	SCALE
JBO	8/22/18	MGH	NONE
SHEET 2 OF 2			SIZE
			A

00A	8/22/18	JBO	MGH	EOS	SEE SHEET 1 FOR REVISION CONTROL	00173EAA_DC
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[ISTPH6X0.3MTL](#) [ISTPH6X4MBL](#) [ISTPH6X5MTL](#) [ISTPH6X3.5MBL](#) [ISTPH6X0.6MTL](#) [ISTPH6X4.5MTL](#)
[ISTPH6X7MTL](#) [ISTPH6X2.5MTL](#) [ISTPH6X1.5MBL](#) [ISTPH6X0.6MBL](#) [ISTPH6X3MBL](#) [ISTPH6X10MBL](#)
[ISTPH6X4MTL](#) [ISTPH6X2MBL](#) [ISTPH6X3.5MTL](#) [ISTPH6X0.3MBL](#) [ISTPH6X2MTL](#) [ISTPH6X1.5MTL](#)
[ISTPH6X4.5MBL](#) [ISTPH6X7MBL](#) [ISTPH6X2.5MBL](#) [ISTPH6X1MTL](#) [ISTPH6X20MBL](#) [ISTPH6X10MTL](#)
[ISTPH6X3MTL](#) [ISTPH6X5MBL](#) [ISTPH6X20MTL](#)