

Specifications

Packaging Detail

Resources

Related Products

Top of Page ^

Home / Products / Copper Systems / Industrial Copper Systems / Industrial Copper Cable / IFC6C04BBL-CG-S



IFC6C04BBL-CG-S

Share

Copper Cable

Copper Cable, Industrial, Cat6, 4-pair, 26/7 AWG stranded, F/UTP, CM, Black, 1000ft/305m reel.

Q

Find A Distributor

Qty

Add to Bom

Specifications

Jacket Material	Polyvinyl chloride
Maximum Installation Temperature (°C)	75
Minimum Installation Temperature (°C)	-20
Minimum Installation Temperature (°F)	-4

Specifications

Packaging Detail

Resources

Related Products

Top of Page ^

Min. Order Qty.	1,000
-----------------	-------

Packaging Detail

UPC	07498388007
Std. Pkg. Qty.	1000
Std. Pkg. Volume (cf)	1.7778
Std. Ctn. Qty.	0
Std. Ctn. Volume (cf)	0.0000

Related Products



ISFX5502ATL-LED



ISFCH5C04ABL-XG



ISFCH5C04ATL-XG

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[IFC6C04BBL-CG-S](#)