



Q

Keyword, Part Number or Cross-Ref

All Products

Solutions

Support

Bill of Materials

Home / Products / Copper Systems / Connectors / Jack Modules / [CJLR6X88TGAW](#)



CJLR6X88TGAW

Share

UTP Jack Module

Cat 6A Left/Right 45 Degree Angled TG Jack Module, Arctic White

Q

Find A Distributor

Qty

Add to Bom

Specifications

Packaging Detail

Resources

Related Products

Top of Page

Specifications

Performance Level	Category 6A
Connector Type	Jack Module
Termination Style	TG Style
Body Material	ABS
Contact Material	Phosphor Bronze

Module Type	Mini-Com
Wiring Scheme	T568A/T568B
Number of Contacts	8
Number of Positions	8
Shield Type	Unshielded (UTP)
Connector 1 Type	RJ45
Connector 2 Type	Wire Cap
Sub Brand	PanNet
Maximum Operating Temperature (°C)	65
Maximum Operating Temperature (°F)	149
Minimum Operating Temperature (°C)	-10
Minimum Operating Temperature (°F)	14
Maximum Storage Temperature (°C)	70
Maximum Storage Temperature (°F)	158
Minimum Storage Temperature (°C)	-40
Minimum Storage Temperature (°F)	-40
Resistance Properties	Heat-Resistant
Color	Arctic White
Product Type	UTP Jack Module
RoHS Compliancy Status	Compliant
Min. Order Qty.	1

Packaging Detail

UPC	61305644939
Std. Pkg. Qty.	1
Std. Pkg. Volume (cf)	0.0032

Std. Ctn. Qty.	50
Std. Ctn. Volume (cf)	0.1604

Resources

Specification Sheets	45° Angled Wire Caps for Mini-Com UTP Jack Modules	US English	View PDF (795.37KB)	Download PDF	Share PDF
Part Drawings	TX6A 10Gig Category 6a Jack Module with Left/Right Wire Cap Assembly	US English	View DXF (3.75MB)	Download DXF	Share DXF
Part Drawings	TX6A 10Gig Category 6a Jack Module with Left/Right Wire Cap Assembly	US English	View DWG (460.79KB)	Download DWG	Share DWG

Related Products



CJ688TGBU

The Category 6, RJ45, 8-position, 8-wire, UTP Mini-Com® universal jack module has TG-style termination and is blue.



CJ688TGBL

The Category 6, RJ45, 8-position, 8-wire, UTP Mini-Com® universal jack module has TG-style termination and is black.



CJS6X88TGY

Category 6A, RJ45, 10 Gb/s, 8-position, 8-wire universal shielded black module with integral shield.



Email Support

Email support available 24/7



800-777-3300

Monday through Thursday 7:00 am-6:30 pm
CST Friday 7:00 am-6:00 pm CST



Where to Buy

Find a Panduit Distributor or Partner

About Us

Research and
Development

Awards

Partner Ecosystem

World
Headquarters

Company Profile

Media Resources

Case Studies

Panduit Code of
Conduct

Careers at Panduit

The Hub – Partner Portal

Product Registration

Panduit Connections Blog



Get Our Catalog

Download the PDF or request a copy be mailed to you.

Which catalog would you like?



Download



Copyright 2019 Panduit

[Legal Information](#) [Privacy Policy](#) [Unsubscribe](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[CJLR6X88TGAW](#)