



Keyword, Part Number or Cross-Ref

[All Products](#)

[Solutions](#)

[Support](#)

[Bill of Materials](#)

[Home](#) / [Products](#) / [Copper Systems](#) / [Connectors](#) / [Jack Modules](#) / [CJLR6X88TGVL](#)



CJLR6X88TGVL

Share

[UTP Jack Module](#)

Cat 6A Left/Right 45 Degree Angled TG Jack Module, Violet

[Find A Distributor](#)

Qty

Add to Bom

[Specifications](#)

[Packaging Detail](#)

[Resources](#)

[Related Products](#)

[Top of Page](#)

Specifications

Performance Level	Category 6A
Connector Type	Jack Module
Termination Style	TG Style
Body Material	ABS
Contact Material	Phosphor Bronze

Module Type	Mini-Com
Wiring Scheme	T568A/T568B
Number of Contacts	8
Number of Positions	8
Shield Type	Unshielded (UTP)
Connector 1 Type	RJ45
Connector 2 Type	Wire Cap
Sub Brand	PanNet
Maximum Operating Temperature (°C)	65
Maximum Operating Temperature (°F)	149
Minimum Operating Temperature (°C)	-10
Minimum Operating Temperature (°F)	14
Maximum Storage Temperature (°C)	70
Maximum Storage Temperature (°F)	158
Minimum Storage Temperature (°C)	-40
Minimum Storage Temperature (°F)	-40
Resistance Properties	Heat-Resistant
Color	Violet
Product Type	UTP Jack Module
RoHS Compliancy Status	Compliant
Min. Order Qty.	1

Packaging Detail

UPC	61305644948
Std. Pkg. Qty.	1
Std. Pkg. Volume (cf)	0.0032

Std. Ctn. Qty.	50
Std. Ctn. Volume (cf)	0.1604

Resources

Specification Sheets	45° Angled Wire Caps for Mini-Com UTP Jack Modules	US English	View PDF (795.37KB)	Download PDF	Share PDF
Part Drawings	TX6A 10Gig Category 6a Jack Module with Left/Right Wire Cap Assembly	US English	View DXF (3.75MB)	Download DXF	Share DXF
Part Drawings	TX6A 10Gig Category 6a Jack Module with Left/Right Wire Cap Assembly	US English	View DWG (460.79KB)	Download DWG	Share DWG

Related Products



CJ688TGBU

The Category 6, RJ45, 8-position, 8-wire, UTP Mini-Com® universal jack module has TG-style termination and is blue.



CJ688TGBL

The Category 6, RJ45, 8-position, 8-wire, UTP Mini-Com® universal jack module has TG-style termination and is black.



CJS6X88TGY

Category 6A, RJ45, 10 Gb/s, 8-position, 8-wire universal shielded black module with integral shield.



Email Support

Email support available 24/7



800-777-3300

Monday through Thursday 7:00 am-6:30 pm
CST Friday 7:00 am-6:00 pm CST



Where to Buy

Find a Panduit Distributor or Partner

About Us

Research and
Development

Awards

Partner Ecosystem

World
Headquarters

Company Profile

Media Resources

Case Studies

Panduit Code of
Conduct

Careers at Panduit

The Hub – Partner Portal

Product Registration

Panduit Connections Blog



Get Our Catalog

Download the PDF or request a copy be mailed to you.

Which catalog would you like?



Download



Copyright 2019 Panduit

[Legal Information](#) [Privacy Policy](#) [Unsubscribe](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[CJLR6X88TGV](#)