



Q

Keyword, Part Number or Cross-Ref

All Products

Solutions

Support

Bill of Materials

Home / Products / Copper Systems / Connectors / Jack Modules / [CJLR6X88TGEI](#)



CJLR6X88TGEI

Share

UTP Jack Module

Cat 6A Left/Right 45 Degree Angled TG Jack Module, Electric Ivory

Q

Find A Distributor

Qty

Add to Bom

Specifications

Packaging Detail

Resources

Related Products

Top of Page

Specifications

|                   |                 |
|-------------------|-----------------|
| Performance Level | Category 6A     |
| Connector Type    | Jack Module     |
| Termination Style | TG Style        |
| Body Material     | ABS             |
| Contact Material  | Phosphor Bronze |

|                                    |                  |
|------------------------------------|------------------|
| Module Type                        | Mini-Com         |
| Wiring Scheme                      | T568A/T568B      |
| Number of Contacts                 | 8                |
| Number of Positions                | 8                |
| Shield Type                        | Unshielded (UTP) |
| Connector 1 Type                   | RJ45             |
| Connector 2 Type                   | Wire Cap         |
| Sub Brand                          | PanNet           |
| Maximum Operating Temperature (°C) | 65               |
| Maximum Operating Temperature (°F) | 149              |
| Minimum Operating Temperature (°C) | -10              |
| Minimum Operating Temperature (°F) | 14               |
| Maximum Storage Temperature (°C)   | 70               |
| Maximum Storage Temperature (°F)   | 158              |
| Minimum Storage Temperature (°C)   | -40              |
| Minimum Storage Temperature (°F)   | -40              |
| Resistance Properties              | Heat-Resistant   |
| Color                              | Electric Ivory   |
| Product Type                       | UTP Jack Module  |
| RoHS Compliancy Status             | Compliant        |
| Min. Order Qty.                    | 1                |

### Packaging Detail

|                       |             |
|-----------------------|-------------|
| UPC                   | 61305644942 |
| Std. Pkg. Qty.        | 1           |
| Std. Pkg. Volume (cf) | 0.0032      |

|                       |        |
|-----------------------|--------|
| Std. Ctn. Qty.        | 50     |
| Std. Ctn. Volume (cf) | 0.1604 |

### Resources

|                      |                                                                      |            |                                     |                              |                           |
|----------------------|----------------------------------------------------------------------|------------|-------------------------------------|------------------------------|---------------------------|
| Specification Sheets | 45° Angled Wire Caps for Mini-Com UTP Jack Modules                   | US English | <a href="#">View PDF (795.37KB)</a> | <a href="#">Download PDF</a> | <a href="#">Share PDF</a> |
| Part Drawings        | TX6A 10Gig Category 6a Jack Module with Left/Right Wire Cap Assembly | US English | <a href="#">View DXF (3.75MB)</a>   | <a href="#">Download DXF</a> | <a href="#">Share DXF</a> |
| Part Drawings        | TX6A 10Gig Category 6a Jack Module with Left/Right Wire Cap Assembly | US English | <a href="#">View DWG (460.79KB)</a> | <a href="#">Download DWG</a> | <a href="#">Share DWG</a> |

### Related Products



#### CJ688TGBU

The Category 6, RJ45, 8-position, 8-wire, UTP Mini-Com® universal jack module has TG-style termination and is blue.



#### CJ688TGBL

The Category 6, RJ45, 8-position, 8-wire, UTP Mini-Com® universal jack module has TG-style termination and is black.



#### CJS6X88TGY

Category 6A, RJ45, 10 Gb/s, 8-position, 8-wire universal shielded black module with integral shield.



## Email Support

Email support available 24/7



## 800-777-3300

Monday through Thursday 7:00 am-6:30 pm  
CST Friday 7:00 am-6:00 pm CST



## Where to Buy

Find a Panduit Distributor or Partner

About Us

Research and  
Development

Awards

Partner Ecosystem

World  
Headquarters

Company Profile

Media Resources

Case Studies

Panduit Code of  
Conduct

Careers at Panduit

The Hub – Partner Portal

Product Registration

Panduit Connections Blog



## Get Our Catalog

Download the PDF or request a copy be mailed to you.

Which catalog would you like?



Download



Copyright 2019 Panduit

[Legal Information](#) [Privacy Policy](#) [Unsubscribe](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[CJLR6X88TGEI](#)