





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PART#	COLOR	DESCRIPTION	WEIGHT*
CJS688TGY	BLACK	8 POSITION, 8 WIRE SHIELDED MODULE WITH INTEGRAL SHIELD. WIRE CAP LABEL IS COLOR CODED FOR T568A AND T568B WIRING SCHEMES.	3.314 LB/100 PCS (1503g/100 PCS)
CJS688TGRDY	RED		
CJS688TGBUY	BLUE		
CJS688TGGRY	GREEN		
CJS688TGVLY	VIOLET		
CJS688TGYLY	YELLOW		

\*WEIGHT IS APPROXIMATE

- NOTES:
1. WHITE WIRE CAP DESIGNATES CATEGORY 6 PERFORMANCE.
  2. MATERIAL:  
MODULE HOUSING-ABS  
SHIELD-TIN PLATED OVER PHOS. BRONZE  
WIRE CAP/CLIP - ZINC AND PC
  3. ALL TX6 PLUS, 8 POSITION, 8 WIRE JACK MODULES ARE UNIVERSAL IN DESIGN. THEY ACCEPT SIX AND EIGHT POSITION MODULAR PLUGS WITHOUT DAMAGE.
  4. DIMENSIONS IN PARENTHESES ARE IN METRIC.
  5. .187 x .010" GROUNDING TAB PROVIDED AS OPTIONAL CONDUCTIVE PATH FOR GROUNDING.



PART NUMBER		CJS688TG**Y	
TITLE			
TX6 PLUS SHIELDED JACK MODULE			
CUSTOMER DRAWING			
ITEM REVISION NAME		M02479NS/08	
DATASET FILE NAME		M02479NS_DC357/08A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ]		MATERIAL:	
.X ± .XX ± .03 [ .8 ]		SEE NOTE 2	
.XXX ± .010 [ .3 ]		DRAWING NUMBER:	
ANGLES ±		02479-357	
THIRD ANGLE PROJECTION			
DRAWN BY	DATE	CHK	SCALE
AFW	3-11-06	CEF	FULL
SHT 1 OF 1			SIZE
			A

5	2-16-17	ROJC	NAGL	TMBA	MODEL REVISION UPDATED REMOVED PREVIOUS REVISIONS FOR CLARITY.	02479-357
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[CJS688TGY-C](#)