


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:

1. SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS AND TO INDICATE PACKAGE QUANTITY.
2. GIGA-PUNCH CONNECTOR ON ONE END AND AN RJ45 MODULAR PLUG WIRED TO EIA/TIA 568B ON THE OTHER END. PATCH CORDS CAN BE USED WITH GIGA-PUNCH CONNECTING BLOCKS.
3. THE GIGA-PUNCH PATCH CORD IS POLARIZED TO PREVENT REVERSE INSTALLATION ON THE CONNECTOR BLOCK, INCORPORATES A CABLE JACKET RETENTION FEATURE WHICH MINIMIZES WIRE UNTWISTING, AND HAS AN INTEGRAL STRAIN RELIEF.
4. PATCH CORDS CONSTRUCTED USING UL OR ETL VERIFIED CABLE.
5. MATERIAL:

CONNECTOR: POLYCARBONATE
CABLE: CAT6, 24 AWG STRANDED-TIN/COPPER
JACKET: PVC
JACKET COLOR: GREY

6. THIS CABLE SHOULD ONLY BE USED IN INTERCONNECT APPLICATIONS.



PANDUIT PART NUMBER	MIN. CABLE LENGTH	WEIGHT
GPPC41G1B	1 FT.	.46 LB/10 PCS (210 g/10 PCS)
GPPC41G3B	3 FT.	.91 LB/10 PCS (411 g/10 PCS)
GPPC41G5B	5 FT.	1.34 LB/10 PCS (607 g/10 PCS)
GPPC41G7B	7 FT.	1.85 LB/10 PCS (838 g/10 PCS)
GPPC41G9B	9 FT.	2.30 LB/10 PCS (1041 g/10 PCS)
GPPC41G14B	14 FT.	3.42 LB/10 PCS (1550 g/10 PCS)
GPPC41G20B	20 FT.	4.79 LB/10 PCS (2172 g/10 PCS)

TIP/RING COLORS

CAD FILENAME/LAYERS		M00245BU_DC_00B.PRT	
PANDUIT CORP. TINLEY PARK, ILLINOIS			
GIGA-PUNCH TO RJ-45 EIA/TIA 568B PATCHCORD (GPPC41G**B) CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± .010(.3) (.XX) ± .03(.8) ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
DRAWN BY S.OLEWINSKI		SCALE NONE	
DATE 7/15/99		DRAWING NO. 00245-17	
CHK'D WOT		DWG A SIZE	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[GPPC4IG3B](#) [GPPC4IG5B](#) [GPPC4IG7B](#)