

IndustrialNet™ TX5e™ Patch Cords

PANDUIT®

SPECIFICATION SHEET

specifications

Industrial Ethernet patch cords shall be constructed of Category 5e, industrial grade, stranded, twisted pair cable for UTP and STP installations. Each patch cord shall be pre-terminated to include Category 5e industrial plugs on each end which are wired according to the T568B standard. Tethered caps shall be available to protect connectivity in un-mated conditions. An IP67 rating shall be achieved when mated with an IP67 industrial grade, bayonet style connector.



technical information

Category 5e/Class D channel and component performance:	Exceeds channel and component requirements of ANSI/TIA-568-C.2 Category 5e and ISO11801 Class D standards at swept frequencies 1 to 100 MHz
FCC and ANSI compliance:	Meets ANSI/TIA/EIA-968-A; contacts plated with 50 microinches of gold for superior performance
IEC compliance:	Patch Cords meets IEC 60603-7; Housing meets IEC 61076-3-106 variant 1, conforms to ODVA specifications
UL compliance:	Outer cable jacket material meets UL 1581 section 480 and 1200 standard for UV and oil resistance respectively
PoE compliance:	Meet requirements of IEEE 802.3af and IEEE 802.3at for PoE applications
Materials:	Constructed of 24 AWG UTP or 26 AWG shielded, stranded industrial grade cable, IndustrialNet™ TX5e™ Modular Plugs and IP67 fittings
Temperature rating:	-4°F to 158°F (-20°C to 70°C) during operation

key features and benefits

Durability	Allows for 100-meter patch runs between automation devices and controls in extremely harsh conditions or environments – common in the automotive, food and beverage, petro-chemical, mining and building automation markets
IP rated	When patch cord plug fittings are mated to IP67 IndustrialNet™ TX5e™ Connectors, the patch cords meet IP67 protection Withstands harsh environments without loss of performance in washdown and temporary submerged conditions
Bayonet-style termination	Provides quick installation for lowest installed cost Mated bayonet tactile lock ensures positive mating between the plug and connector
100% performance tested	Confidence that each patch cord delivers Category 5e performance at the component level

applications

The IndustrialNet™ TX5e™ Patch Cords provide reliability and high performance, as an integral component to the end-to-end solution, for Industrial Network applications. In the mated conditions, these patch cords can withstand high temperature and high vibration, commonly found in metal forming or

automotive manufacturing. The IP67 rating is imperative in the food and beverage industries where wash down is common. Pre-integrated tethered caps allow for the plugs to be protected in their unmated condition, such as during shipping, storage, installation or maintenance.

www.panduit.com

IndustrialNet™ TX5e™ Patch Cords

UTP with caps:	IUTPCH*BLY
UTP without caps:	IUTPCHNC*BLY
STP with caps:	ISTPCH**MBLY
STP without caps:	ISTPCHNC**MBLY

IndustrialNet™ TX5e™ Connectors

UTP:	IAEBH5E
Shielded:	IAEBH5ES

IndustrialNet™ TX5e™ Coupler

UTP:	IAEBHC5E
-------------	----------

IndustrialNet™ Enclosures and Accessories

Enclosure:	IAEIP66
Populated gland plate:	IAECGP
Blank gland plate:	IAEBGP
Fan kit:	IAEFK54
15" TX5e™ patch cord:	IUTPCHBH1.25BLY
Empty bulkhead:	IAEBH

IndustrialNet™ Stainless Steel Faceplates


Single gang:	IAEFP1
Double gang:	IAEFP2-2G

*For lengths 3, 5, 7, 10, 15 or 20 feet, change the length designation in the part number to the desired length. For example, the part number for a 7-foot, UTP patch cord is IUTPCH7BLY.


**For lengths 1, 2, 3 or 5 meters, change the length designation in the part number to the desired length. For example, the part number for a 5-meter, shielded patch cord is ISTPCH5MBLY.

IndustrialNet™ TX5e™ Patch Cords

Patch Cord With Caps



Patch Cord Without Caps



WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA
Markham, Ontario
cs-cdn@panduit.com
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
cs-emea@panduit.com
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
cs-ap@panduit.com
Phone: 65.6305.7575

PANDUIT JAPAN
Tokyo, Japan
cs-japan@panduit.com
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA
Guadalajara, Mexico
cs-la@panduit.com
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
cs-aus@panduit.com
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com

Contact Customer Service by email: cs@panduit.com
or by phone: 800.777.3300 and reference COSP122

PANDUIT®

©2011 Panduit Corp.
ALL RIGHTS RESERVED.

WW-COSP122

4/2011

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[IUTPCH20BLY](#) [IUTPCH15BLY](#) [IUTPCH7BLY](#) [IUTPCH3BLY](#) [IUTPCH5BLY](#) [IUTPCH10BLY](#)