


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

TX6 UTP 28AWG
PATCH CORDS

PANDUIT PART NUMBER	MIN. CABLE LENGTH	PANDUIT PART NUMBER	MIN. CABLE LENGTH
UTP28SP1**	1 FT.	UTP28SP0.5M**	0.5 METER
UTP28SP2**	2 FT.	UTP28SP1M**	1 METER
UTP28SP3**	3 FT.	UTP28SP1.5M**	1.5 METER
UTP28SP4**	4 FT.	UTP28SP2M**	2 METER
UTP28SP5**	5 FT.	UTP28SP2.5M**	2.5 METER
UTP28SP6**	6 FT.	UTP28SP3M**	3 METER
UTP28SP7**	7 FT.	UTP28SP3.5M**	3.5 METER
UTP28SP8**	8 FT.	UTP28SP4M**	4 METER
UTP29SP9**	9 FT.	UTP29SP4.5M**	4.5 METER
UTP28SP10**	10 FT.	UTP28SP5M**	5 METER
UTP28SP11**	11 FT.	UTP28SP5.5M**	5.5 METER
UTP28SP12**	12 FT.	UTP28SP6M**	6 METER
UTP28SP13**	13 FT.	UTP28SP7M**	7 METER
UTP28SP14**	14 FT.	UTP28SP8M**	8 METER
UTP28SP15**	15 FT.	UTP28SP9M**	9 METER
UTP28SP16**	16 FT.	UTP28SP10M**	10 METER
UTP28SP17**	17 FT.	UTP28SP11M**	11 METER
UTP28SP18**	18 FT.	UTP28SP12M**	12 METER
UTP28SP19**	19 FT.	UTP28SP13M**	13 METER
UTP28SP20**	20 FT.	UTP28SP14M**	14 METER
UTP28SP25**	25 FT.	UTP28SP15M**	15 METER
UTP28SP30**	30 FT.		
UTP28SP35**	35 FT.		
UTP28SP40**	40 FT.		
UTP28SP45**	45 FT.		
UTP28SP50**	50 FT.		

1	5-22-12	BJN	MATO	SEE SHEET 1 FOR REVISIONS	11M215BG-02	MATO	EJH		
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH

MODEL FILENAME		SIZE A
DRAWING FILENAME 11M215BG_DC02/00B		
TX6 UTP 28AWG COPPER PATCH CORDS (CM/LSZH) CUSTOMER DRAWING		
 TINLEY PARK, IL 60487		I.I. NUMBER
		PRODUCT SPEC/ PKG SPEC
	ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ±.06(1.5)(.XXX) ±.010(.3) (.XX) ± ANGLES ±	ASSY METHOD/ TEST METHOD
		SCALE NONE
DRAWN BY BJN	REVIEW DRAWING NUMBERS	PART NO. UTP28SPXX**
DATE 5-11-12	MAT'L	DRAWING NO. 11M215BG-02 SHEET 2 OF 2
CHK'D MATO		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[UTP28SP10](#) [UTP28SP2](#) [UTP28SP6](#) [UTP28SP7](#) [UTP28SP8](#) [UTP28SP15](#) [UTP28SP4](#) [UTP28SP5](#) [UTP28SP14](#)
[UTP28SP3](#) [UTP28SP9](#) [UTP28SP20](#) [UTP28SP25](#) [UTP28SP1](#) [UTP28SP2M](#) [UTP28SP3M](#) [UTP28SP15M](#)
[UTP28SP7M](#) [UTP28SP30](#) [UTP28SP35](#) [UTP28SP50](#) [UTP28SP3.5M](#) [UTP28SP4M](#) [UTP28SP1M](#) [UTP28SP0.5M](#)
[UTP28SP5.5M](#) [UTP28SP8M](#) [UTP28SP17](#) [UTP28SP12M](#) [UTP28SP13](#) [UTP28SP11M](#) [UTP28SP19](#) [UTP28SP13M](#)
[UTP28SP9M](#) [UTP28SP11](#) [UTP28SP45](#) [UTP28SP40](#) [UTP28SP18](#) [UTP28SP10M](#) [UTP28SP5M](#) [UTP28SP14M](#)
[UTP28SP12](#) [UTP28SP16](#) [UTP28SP2.5M](#) [UTP28SP4.5M](#) [UTP28SP6M](#) [UTP28SP1.5M](#)