

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




FIGURE 1

NOTES:

1. TX6A-SD 10GIG UTP PLUG-TO-PLUG ZONE CORD
2. 100% PERFORMANCE TESTED TO CATEGORY 6A PERMANENT LINK LIMITS.
3. TERMINATED WITH (8 POSITION) RJ45 MODULAR PLUGS AT BOTH ENDS PER T568B
4. CONSTRUCTED WITH 26AWG SOLID CATEGORY 6A UTP RISER, PLENUM, AND LOW SMOKE ZERO HALOGEN CABLE
5. MATERIALS:
PLUG: POLYCARBONATE
BOOT: CLEAR PVC




FIGURE 2

SEE SHEET 2 FOR ZONE CORD LENGTHS AND PART NUMBERS

PART NUMBER UXP* SERIES	PRODUCT SPEC/PKG SPEC N/A
I.T. NUMBER N/A	WORK INSTRUCTION N/A
TITLE TX6A-SD 10GIG UTP PLUG-TO-PLUG ZONE CORD	
CUSTOMER DRAWING	
ITEM REVISION NAME 09M129BG/01	
DATASET FILE NAME 09M129BG_DC02/01A	PANDUIT
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]	MATERIAL:
.x ± .06 [1.5]	.xxx ± .010 [.3]
.xx ±	ANGLES ±
	THIRD ANGLE PROJECTION
DRAWING NUMBER: 09M129BG - 02	
DRAWN BY BJN	DATE 3-22-10
CHK KSM	SCALE NONE
SHT 1 OF 2	
REV	DATE
BY	CHK
APR	
DESCRIPTION	
ECN	

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

10GIG SD UTP PLUG-TO-PLUG ZONE CORDS

PART NUMBERS		PART NUMBERS
UXPPBU** (PLENUM)		UXPLWH**M
UXPRBU** (RISER)		(LSZH)
MIN. CABLE LENGTH		MIN. CABLE LENGTH
10 FT (120 ^{**})		4 METERS (158 ^{**})
15 FT (180 ^{**})		5 METERS (197 ^{**})
20 FT (240 ^{**})		6 METERS (237 ^{**})
25 FT (300 ^{**})		7 METERS (276 ^{**})
30 FT (360 ^{**})		8 METERS (315 ^{**})
35 FT (420 ^{**})		9 METERS (355 ^{**})
40 FT (480 ^{**})		10 METERS (394 ^{**})
45 FT (540 ^{**})		11 METERS (434 ^{**})
50 FT (600 ^{**})		12 METERS (473 ^{**})
55 FT (660 ^{**})		13 METERS (512 ^{**})
60 FT (720 ^{**})		14 METERS (552 ^{**})
65 FT (780 ^{**})		15 METERS (591 ^{**})
70 FT (840 ^{**})		16 METERS (630 ^{**})
75 FT (900 ^{**})		18 METERS (709 ^{**})
80 FT (960 ^{**})		20 METERS (788 ^{**})
85 FT (1020 ^{**})		22 METERS (867 ^{**})
90 FT (1080 ^{**})		24 METERS (945 ^{**})
95 FT (1140 ^{**})		25 METERS (985 ^{**})
100 FT (1200 ^{**})		26 METERS (1024 ^{**})
110 FT (1320 ^{**})		28 METERS (1103 ^{**})
120 FT (1440 ^{**})		30 METERS (1182 ^{**})
130 FT (1560 ^{**})		32 METERS (1260 ^{**})
140 FT (1680 ^{**})		34 METERS (1339 ^{**})
150 FT (1800 ^{**})		36 METERS (1418 ^{**})
		38 METERS (1497 ^{**})
		40 METERS (1575 ^{**})
		42 METERS (1654 ^{**})
		44 METERS (1733 ^{**})
		46 METERS (1812 ^{**})
		48 METERS (1890 ^{**})
		50 METERS (1969 ^{**})

D10100DA/14

1 12-13-13 BJT EJH EJH SEE SHEET 1 FOR REVISIONS

09M129BG-02

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE		SIZE
							BJN	3-22-10	KSM	NONE	SHT 2 OF 2	A

PLENUM, AND RISER OFFERED WITH BLUE CABLE. (FEET ONLY)
LSZH OFFERED WITH WHITE CABLE. (METERS ONLY)

STRAIN RELIEF BOOTS AVAILABLE IN CLEAR ONLY.

**=LENGTH (SEE FIGURE 2, SHEET 1)

PART NUMBER UXP* SERIES	PRODUCT SPEC/PKG SPEC N/A
I.T. NUMBER N/A	WORK INSTRUCTION N/A
TITLE	
TX6 10GIG UTP -PLUG-TO-PLUG SD ZONE CORD	
ITEM REVISION NAME 09M129BG/01	CUSTOMER DRAWING
DATASET FILE NAME 09M129BG_DC02/01A	PANDUIT
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]	MATERIAL:
.x ± .06 [1.5] .xx ± .010 [.3] ANGLES ±	
	THIRD ANGLE PROJECTION
DRAWING NUMBER: 09M129BG - 02	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[UXPPBU10](#) [UXPRBU75](#) [UXPRBU50](#) [UXPRBU25](#) [UXPRBU60](#) [UXPRBU140](#)