




PANDUIT P/N	WEIGHT
PVQ-EPC28	0.2 LB EA. 92g EA.

NOTES:
1. DIMENSIONS IN BRACKETS ARE IN METRIC.
2. PART INCLUDES:
(1) PANVIEW IQ EXPANSION PORT CABLE 28in (PVQ-EPC28)



MODEL FILENAME m02676hb_rs485_01.sldprt		SIZE A
DRAWING FILENAME M02676HB_DC117_00A.slddrw		
PanView iQ Expansion Port Cable, 28in/0.71m CUSTOMER DRAWING		
 TINLEY PARK, ILL 60477	I.L. NUMBER N/A	
	PRODUCT SPEC/ PKG SPEC N/A	
	ASSEMBLY METHOD/ TEST METHOD N/A	
	SCALE NONE	
 THIRD ANGLE PROJECTION	ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ±.03 (.XXX) ±.005 (.XX) ±.01 ANGLES ±1°	
DRAWN BY ALP	REVIEW DRAWING NUMBERS	PART NO. PVQ-EPC28
DATE 1/31/11		
CHK'D MJD	MAT'L: SEE NOTES ABOVE	DRAWING NO. 02676-117 Sheet 1 of 1

R	1/31/11	ALP	MJD	RELEASE TO PRODUCTION	02676-117	MJD	MJD		
REV.	DATE	BY	CHK D	DESCRIPTION	ECN	ECN REV	CUS T	S UP	GM BH

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

PVQ-EPC28