

Search within category

BUY NOW

DESIGN / INSTALL



TM1S4-M

Cable tie mount - screw applied, .32" (8.1mm)W, #4 (M2.5), nylon, bulk package.

Specs	Packaging Details	Documents	★ Add to Favorites	🛒 Add to BOM
Mounting Method	#4 (M2.5) Screw			
Material	Nylon 6.6			
UL Recognized	E136577			
Hole Diameter (mm)	3			
Screw Size Metric	M2.5			
Counterbore Diameter In.	0.23			
Height (In.)	0.23			
Length (In.)	0.51			
Width (In.)	0.32			
Color	Natural			
Max. Continuous Use Temperature	-76°F (-60°C) - 185°F (85°C)			
Temperature Range	-76°F - 185°F (-60°C - 85°C)			
RoHS Compliancy Status	Compliant			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[TM1S4-M](#)