

Search within category

GO

BUY NOW

DESIGN / INSTALL



TM1S6-C0

The cable tie mount in black is applied with a #6 (M3) screw and is 0.32" (8.1 mm) wide. It is made of weather-resistant nylon 6.6, which increases mechanical strength, heat and wear resistance, and stiffness in outdoor environments. It comes in packages of 100.

Specs

Packaging Details

Documents

★ Add to Favorites

🛒 Add to BOM

Compatible Cable Tie	M
Mount Method	#6 (M3) Screw
Material	Weather Resistant Nylon 6.6
Overall Length (In.)	0.51
Overall Length (mm)	16
Overall Width (In.)	0.32
Overall Width (mm)	10.8
Environment	Outdoor
Color	Black
Flammability Rating	UL94V-2
CE Compliant	Yes
UL Recognized (File #E136577)	Yes
Hole Diameter (In.)	0.14
Hole Diameter (mm)	3.7
Screw Size	#6 (M3)
Counterbore Diameter In.	0.28
Counterbore Diameter mm	7.0
Temperature Range	-40°F - 185°F (-40°C - 85°C)
UL Recognized	E136577
RoHS Compliancy Status	Compliant
Min. Order Qty.	100
Product Type	Cable Tie Mounts - Screw Applied

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[TM1S6-C0](#)