

## TM1S6-M30



### Cable Tie Mounts - Screw Applied

The cable tie mount in black is applied with a #6 (M3) screw and is 0.32" (8.1 mm) wide. It is made of heat-stabilized nylon 6.6, which increases mechanical strength, heat and wear resistance, and stiffness in indoor environments. It comes in packages of 1000.

Q Find A Distributor

Qty

Add to Bom

- Specifications
- Packaging Detail
- Resources
- Related Products



### Specifications

Top of Page

^

Compatible Cable Tie	M
Mount Method	#6 (M3) Screw
Material	Heat Stabilized Nylon 6.6
Overall Length (In.)	0.51
Overall Length (mm)	13
Overall Width (In.)	0.32
Overall Width (mm)	8.1
Environment	Indoor
Color	Black
Flammability Rating	UL94V-2
CE Compliant	Yes
CE Marking	Yes
UL Recognized (File #E136577)	Yes
Hole Diameter (In.)	0.14
Hole Diameter (mm)	3.7
Screw Size	#6 (M3)
Counterbore Diameter In.	0.28
Counterbore Diameter mm	7.0
Temperature Range	-76°F - 239°F (-60°C - 115°C)
UL Recognized	E136577
Product Type	Cable Tie Mounts - Screw Applied

### Packaging Detail

UPC	07498358163
Std. Pkg. Qty.	1000
Std. Pkg. Volume (cf)	0.0948
Std. Ctn. Qty.	5000
Std. Ctn. Volume (cf)	0.4739

### Resources

Part Drawings	Part Drawing - PDF - TM1S_R8	English	<div>View PDF (52.55KB)</div>	<div>Download PDF</div>	<div>Share PDF</div>
Part Drawings	Cable Tie Mount TM1S6 STP File	English	<div>View STP (123.00KB)</div>	<div>Download STP</div>	<div>Share STP</div>

### Related Products




#### ABM2S-A-D

The 4-way adhesive backed cable tie mount in white is mounted with rubber adhesive tape. It is 1" long x 1" wide (25.4 x 25.4 mm) and made of ABS material, which increases mechanical strength, heat and wear resistance, and stiffness. It is used with miniature, intermediate, and standard cable ties. It is designed for indoor environments and comes in packages of 500.



#### ABMM-A-D

The 4-way adhesive backed cable tie mount in white is mounted with rubber adhesive tape. It is 0.75" long x 0.75" wide (19.1 x 19.1 mm) and made of ABS plastic. It is used with miniature and intermediate cable ties. It is designed for indoor environments and comes in packages of 500.



#### AST25-5-C100

The aerial support tie in black with integral 1/2" (12.7mm) spacer for support strand applications is made of weather-resistant polypropylene. It is 10.0" long and 0.45" wide (254.0 x 11.4 mm), features a releasable locking style and can support a maximum bundle diameter of 2.5" (63.5 mm). It is designed for outdoor environments and comes in packages of 100.

📍

Email Support

Email support available 24/7

📞

#800-777-3300

Monday through Thursday 7:00 am-6:30 pm  
CST Friday 7:00 am-6:00 pm CST

📍

Where to Buy

Find a Panduit Distributor or Partner

- About Us
- Research and Development
- Awards
- Partner Ecosystem
- World Headquarters
- Company Profile
- Media Resources
- Case Studies
- Panduit Code of Conduct
- Careers at Panduit
- The Hub – Partner Portal
- Product Registration
- Panduit Connections Blog
- 📄

Get Our Catalog

Download the PDF or request a copy be mailed to you.

Which catalog would you like? ▾

Download ▾



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[TM1S6-M30](#)