


NOTES :



1. CONNECTORS MEET REQUIREMENTS OF TIA-568-C.3.
2. ALL MATERIALS AND COMPONENTS MEET THE MATERIAL RESTRICTIONS OF RoHS, (EUROPEAN DIRECTIVE 2011/65/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.
3. FOR PERFORMANCE REQUIREMENTS OR LENGTHS OTHER THAN THOSE SPECIFIED, CONTACT PANDUIT.



- CABLE ASSEMBLY MUST SHIP
WITH DUST CAPS INSTALLED

FIBER TYPE
9 - SINGLEMODE OS2 (YELLOW JACKET)
X - 50/125 OM3 (AQUA JACKET)
Z - 50/125 OM4
FIBER COUNT
T - 12 FIBERS
JACKET FLAME RATING
R - OFNR
CONNECTOR
1 - LC
3 - SC
CONNECTOR VARIANT
7 - 18" BREAKOUT
PERFORMANCE
S - STANDARD PERFORMANCE
UNIT OF MEASURE
M - METERS
LENGTH
001 - 1 METER
002 - 2 METERS
003 - 3 METERS

1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
F		T	S	R		7	N	N	S	N	M			

							TITLE PRETERMINATED 12 STRAND LC/SC FIBER OPTIC PIGTAIL CUSTOMER DRAWING					
							ITEM REVISION NAME M00997BJ/00					
							DATASET FILE NAME M00997BJ_DC/00B					
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .03 [.762] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 1 °					
							 THIRD ANGLE PROJECTION					
							DRAWING NUMBER: M00997BJ-DC					
00B	05-12-17	SAT	WMA	RWB	RELEASED TO PRODUCTION	M00997BJ-DC						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	SIZE
							SAT	09-23-14	WMA	NONE		B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[FXTSR37NNSNM002](#) [F9TSR37NNSNM001](#) [FXTSR17NNSNM002](#) [F9TSR37NNSNM002](#) [F9TSR17NNSNM003](#)
[FXTSR17NNSNM001](#) [F9TSR17NNSNM002](#) [FXTSR37NNSNM001](#) [F9TSR17NNSNM001](#) [FXTSR37NNSNM003](#)
[FXTSR17NNSNM003](#)