



AC15WNA – Two Wire Power Cord for North America




Specifications

- Plug Type: NEMA 1-15P
- Wire Size 18AWG
- Amperage Rating: 10A
- Connector: IEC320 C7
- Temperature: 60°C
- Voltage Rating: 125V

Safety Approvals

- CSA
- UL

Dimension Diagram Unit: inches



Compatibility Guide

Adapters

PSAA15W-050L6
 PSAA15W-120L6
 PSAA15W-180L6
 PSAA15W-240L6
 PSAA15W-480L6
 PSAC45W-120
 PSAC45W-180
 PSAC45W-240
 PSAC45W-480
 PSAC45W-560

PSAC60W-120
 PSAC60W-180
 PSAC60W-240
 PSAC60W-480
 PSAC60W-560
 PSM36W-120L6
 Any R-series adapter fitted
 w/RPX interchangeable AC clip

Power over Ethernet

POE21W-1AF
 POE29W-1AT
 POE29W-560
 POE61W-560D
 POE61W-560DG
 POE16R-1AF/POE16R-1AFG when
 fitted w/RPX interchangeable AC clip

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phihong:](#)

[AC15WNA-R](#)