

## Zack marker strip - ZB 5,LGS:FORTL.ZAHLEN 291-300 - 1050017:0291

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Zack marker strip, 10-section, horizontally labeled with the consecutive numbers: 291 ... 300, white, width: 5 mm

RoHS

### Key Commercial Data

|                        |                                                                                                         |
|------------------------|---------------------------------------------------------------------------------------------------------|
| Packing unit           | 10 pc                                                                                                   |
| Minimum order quantity | 10 pc                                                                                                   |
| GTIN                   | <br>4 017918 506995 |
| GTIN                   | 4017918506995                                                                                           |

### Technical data

#### Dimensions

|           |      |
|-----------|------|
| Width (a) | 5 mm |
|-----------|------|

#### General

|                                        |                                |
|----------------------------------------|--------------------------------|
| Color                                  | white                          |
| Type                                   | high                           |
| Components                             | free from silicone and halogen |
| Flammability rating according to UL 94 | V2                             |
| Material                               | PA                             |
| Wipe resistance                        | DIN 30646                      |
|                                        | DIN VDE 0611                   |
| Printing                               | 291 ... 300                    |

#### Standards and Regulations

|                                        |              |
|----------------------------------------|--------------|
| Wipe resistance                        | DIN 30646    |
|                                        | DIN VDE 0611 |
| Flammability rating according to UL 94 | V2           |

## Zack marker strip - ZB 5,LGS:FORTL.ZAHLEN 291-300 - 1050017:0291

### Classifications

#### eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27141137 |
| eCl@ss 4.0    | 24190200 |
| eCl@ss 4.1    | 24190200 |
| eCl@ss 5.0    | 27141100 |
| eCl@ss 5.1    | 27141100 |
| eCl@ss 6.0    | 27141100 |
| eCl@ss 7.0    | 27141137 |
| eCl@ss 8.0    | 27141137 |
| eCl@ss 9.0    | 27141137 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000761 |
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC000761 |
| ETIM 6.0 | EC000761 |
| ETIM 7.0 | EC000761 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11     | 39121410 |
| UNSPSC 12.01  | 39121410 |
| UNSPSC 13.2   | 39131505 |
| UNSPSC 18.0   | 39131505 |
| UNSPSC 19.0   | 39131505 |
| UNSPSC 20.0   | 39131505 |
| UNSPSC 21.0   | 39131505 |

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

1050017:0291