

## Zack marker strip - ZB 6,LGS:FORTL.ZAHLEN 361-370 - 1051016:0361

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Zack marker strip, 10-section, horizontally labeled with the consecutive numbers: 361 ... 370, white, width: 6 mm

The figure shows the version ZB 6:UNBEDRUCKT



### Key Commercial Data

|                        |                                                                                                         |
|------------------------|---------------------------------------------------------------------------------------------------------|
| Packing unit           | 10 pc                                                                                                   |
| Minimum order quantity | 10 pc                                                                                                   |
| GTIN                   | <br>4 017918 487768 |
| GTIN                   | 4017918487768                                                                                           |

### Technical data

#### Dimensions

|           |      |
|-----------|------|
| Width (a) | 6 mm |
|-----------|------|

#### General

|                                        |                                |
|----------------------------------------|--------------------------------|
| Color                                  | white                          |
| Type                                   | high                           |
| Components                             | free from silicone and halogen |
| Flammability rating according to UL 94 | V2                             |
| Material                               | PA                             |
| Wipe resistance                        | DIN EN 61010-1 (VDE 0411-1)    |
| Printing                               | 361 ... 370                    |

#### Standards and Regulations

|                                        |                             |
|----------------------------------------|-----------------------------|
| Wipe resistance                        | DIN EN 61010-1 (VDE 0411-1) |
| Flammability rating according to UL 94 | V2                          |

## Zack marker strip - ZB 6,LGS:FORTL.ZAHLEN 361-370 - 1051016:0361

### Classifications

#### eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27141137 |
| eCl@ss 4.0    | 24190200 |
| eCl@ss 4.1    | 24190200 |
| eCl@ss 5.0    | 27141100 |
| eCl@ss 5.1    | 27141100 |
| eCl@ss 6.0    | 27141100 |
| eCl@ss 7.0    | 27141137 |
| eCl@ss 8.0    | 27141137 |
| eCl@ss 9.0    | 27141137 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000761 |
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC000761 |
| ETIM 6.0 | EC000761 |
| ETIM 7.0 | EC000761 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11     | 39121410 |
| UNSPSC 12.01  | 39121410 |
| UNSPSC 13.2   | 39131505 |
| UNSPSC 18.0   | 39131505 |
| UNSPSC 19.0   | 39131505 |
| UNSPSC 20.0   | 39131505 |
| UNSPSC 21.0   | 39131505 |

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1051016:0361](#)