

## Protective covers - HC-B 6-TMS-SD-IP65-OLOGO - 1690859

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Protective cover IP65, for panel mounting side, with screw locking and retaining cord. B6, without logo

Photo shows the product with the PC logo

RoHS

### Key Commercial Data

Packing unit	10 STK
GTIN	 4 017918 890742
GTIN	4017918890742

### Technical data

#### Dimensions

Height	31.5 mm
Width	55 mm
Length	90 mm

#### Ambient conditions

Degree of protection of housing (IP)	IP65
Ambient temperature (operation)	-20 °C ... 100 °C

#### General

Size	B6
Type	HC-ADVANCE protective cover
Housing type	Protective cover
Color	gray
Locking type	Screw locking
Torque	3 Nm (Locking screw)
Seal material	NBR
Material lock	Stainless steel

## Protective covers - HC-B 6-TMS-SD-IP65-OLOGO - 1690859

### Technical data

#### General

Material of locking screw	Stainless steel
Material, protective cover	PA
Flammability rating according to UL 94	V0
Assembly instructions	Tightening torque of locking screw: 3 Nm

#### Standards and Regulations

Flammability rating according to UL 94	V0
--	----

#### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

### Approvals


#### Approvals

#### Approvals

#### EAC

#### Ex Approvals

#### Approval details

EAC		RU C- DE.AI30.B.01102
-----	---	--------------------------

Phoenix Contact 2018 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

1690859