

Electronic housing - ME 22,5 OT-MKDSO SET YE - 2706399

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Upper part, color: yellow, width: 22.5 mm, height: 38.5 mm



Your advantages

- ✓ Item is from the ME product range
- ✓ Tool-free mounting
- ✓ Available in overall widths from 12.5 mm to 90 mm, modular extension is possible
- ✓ Inflammability class V0 according to UL 94
- ✓ Variety of connection technologies
- ✓ Can be mounted on the DIN rail
- ✓ Optional bus connector that is either integrated or mounted on the DIN rail

RoHS

Key Commercial Data

Packing unit	10 pc
GTIN	 4 017918 617844
GTIN	4017918617844

Technical data

General

Housing type	Upper part
Housing material	Polyamide
Color (RAL)	yellow (1018)

Dimensions

Height	38.5 mm
Width	22.5 mm
Depth	99 mm

Technical data

Connection in acc. with standard	CUL
----------------------------------	-----

Electronic housing - ME 22,5 OT-MKDSO SET YE - 2706399

Technical data

Technical data

Nominal voltage U_N	300 V
Nominal current I_N	10 A
AWG/kcmil	30-12
Indicator1	CUL1
Number of positions	16

Standards and Regulations

Connection in acc. with standard	CUL
Flammability rating according to UL 94	V0

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Approvals

Approvals

Approvals

cUL Recognized / null / null / null / null / null / null / null / null / null / null / cULus Recognized

Ex Approvals

Approval details

cUL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 60425
	D	B	
Nominal voltage U_N	300 V	300 V	
Nominal current I_N	10 A	10 A	
mm ² /AWG/kcmil	30-12	30-12	

--

--

--

Electronic housing - ME 22,5 OT-MKDSO SET YE - 2706399

Approvals

cULus Recognized



Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

2706399