

Feed-through header - MSTBA 2,5/ 3-G-5,08 RD - 1709823


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

PCB headers, nominal current: 12 A, rated voltage (III/2): 320 V, number of positions: 3, pitch: 5.08 mm, color: red, contact surface: Tin, mounting: Wave soldering




Your advantages

- ✓ Maximum flexibility when it comes to device design – one header for connectors with different connection technologies
- ✓ Well-known mounting principle allows worldwide use
- ✓ Plug-in direction parallel to the PCB
- ✓ Closed contour for optimum stability of the plug-in connection



Key Commercial Data

Packing unit	250 pc
GTIN	 4 055626 204956
GTIN	4055626204956

Technical data

Dimensions

Length [l]	12 mm
Width	17.16 mm
Pitch	5.08 mm
Dimension a	10.16 mm
Width [w]	17.16 mm
Height [h]	12.1 mm
Height	8.6 mm
Length of the solder pin	3.5 mm
Pin dimensions	1 x 1 mm
Length	12 mm

General

Range of articles	MSTBA 2,5/...-G
-------------------	-----------------

Feed-through header - MSTBA 2,5/ 3-G-5,08 RD - 1709823

Technical data

General

Insulating material group	I
Rated voltage (III/2)	320 V
Nominal current I _N	12 A
Flammability rating according to UL 94	V0
Color	red
Number of positions	3

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

1709823