

Electronic housing - ME MAX 22,5 2-2 DEV-KIT KMGY - 2202524

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




DEV-KIT ME MAX: contains 1 x ME MAX 22,5 2-2 housing and pluggable connection technology (4x MSTBO with 4x MSTBT), supplied in individual parts

Your advantages

- ✓ Narrow housing with overall width of 22.5 mm
- ✓ Touch-proof, plug-in connection technology
- ✓ Optional perfboard for soldering THT components by hand
- ✓ Connection of individual housing modules by means of the optional ME TBUS via DIN rail

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 141749
GTIN	4055626141749

Technical data

General

Housing type	Component housing
Housing material	Polyamide
Color (RAL)	light gray

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
---------------------------------	--

Dimensions

Length	99 mm
Height	110 mm
Width	22.5 mm

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Electronic housing - ME MAX 22,5 2-2 DEV-KIT KMGY - 2202524

Technical data

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Approvals


Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		B.01742
-----	---	---------

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

2202524