

Interface module - FLKMS-D15 SUB/S/ZFKKDS/PE - 2295978

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



VARIOFACE module, with spring-cage connection and one D-SUB miniature pin strip, integrated PE contact for connecting the PCB and DIN rail, 15-pos.



Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 448011
GTIN	4017918448011

Technical data

Dimensions

Width	64 mm
Height	90 mm
Depth	62 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
---------------------------------	------------------

General

Max. perm. operating voltage	25 V AC (60 V DC)
Max. perm. current (per branch)	2.5 A
Number of positions	15
Status display	No
Mounting position	any
Degree of protection	IP00

Connection data for connection 1

Connection name	Field level
Connection in acc. with standard	IEC / EN
Connection method	Spring-cage connection

Interface module - FLKMS-D15 SUB/S/ZFKKDS/PE - 2295978

Technical data

Connection data for connection 1

Conductor cross section solid	0.2 mm² ... 2.5 mm²
Conductor cross section flexible	0.2 mm² ... 1.5 mm²
Conductor cross section AWG	24 ... 14
Number of positions	16

Connection data for connection 2

Connection name	Controller level
Connection method	D-SUB pin strip
Number of positions	15

Standards and Regulations

Connection in acc. with standard	CUL
Designation	Air clearances and creepage distances
Standards/regulations	DIN EN 50178: 1998-04
Rated insulation voltage	125 V
Rated surge voltage	1.2 kV (1.2/50 µs)
Insulation	Functional insulation
Degree of pollution	2
Overvoltage category	II

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Approvals

Approvals

Approvals

UL Recognized / cUL Recognized / EAC / cULus Recognized

Ex Approvals

Approval details

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 238705
Nominal voltage UN	125 V		

Interface module - FLKMS-D15 SUB/S/ZFKKDS/PE - 2295978

Approvals

Nominal current I _N	2 A

cUL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 238705
Nominal voltage U _N		125 V	
Nominal current I _N		2 A	

EAC		RU C- DE.A*30.B.01742
-----	---	--------------------------

cULus Recognized	
------------------	---

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

2295978