

Shrink sleeve - WMS 25,4 (60X40)R YE - 0800405

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Shrink sleeve, Roll, yellow, can be labeled with: THERMOMARK ROLLMaster 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL: without print, perforated, mounting type: slide-on, cable diameter range: 8.5 ... 25.4 mm, lettering field size: 60 x 40 mm, Number of individual labels: 250

Your advantages

- ✓ WMS ... shrink sleeves provide permanent and captive conductor and cable marking
- ✓ The sleeves are pre-assembled for optimum use of material
- ✓ The conductor to be marked is simply threaded through the sleeve and fixed by shrinking the sleeve
- ✓ The sleeves remain flexible after shrinking
- ✓ The shrink sleeves provide additional electrical insulation and mechanical protection for the conductors
- ✓ Up to four markers per sleeve are separated by perforations
- ✓ UL 224 (125°C, 600 V, all tubing)
- ✓ CSA.C22.2 No. 198.1 (125°C, 600 V, all tubing)



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 626729
GTIN	4046356626729

Technical data

Dimensions

Length (b)	60 mm
Width (a)	40 mm
Cable diameter	8.5 mm ... 25.4 mm

Ambient conditions

Ambient temperature (operation)	-55 °C ... 135 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.

General

Shrink sleeve - WMS 25,4 (60X40)R YE - 0800405

Technical data

General

Color	yellow
Base element material	polyolefine
Type	Shrink sleeve
Components	halogen-free
Material	Polyolefine
Shrink rate	3:1
RoHS compliant	Yes
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Printing	without print
Number of individual labels	250
Number of individual labels per row	1
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Result of weather resistance test	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result of wipe resistance test	Test passed
Marking mounting type	slide-on

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Classifications

eCl@ss

eCl@ss 10.0.1	27400401
eCl@ss 4.0	24190200
eCl@ss 4.1	24190200
eCl@ss 5.0	27400100
eCl@ss 5.1	27400100
eCl@ss 6.0	27400100
eCl@ss 7.0	27400105
eCl@ss 8.0	27400105
eCl@ss 9.0	27400401

ETIM

ETIM 2.0	EC000761
----------	----------

Shrink sleeve - WMS 25,4 (60X40)R YE - 0800405

Classifications

ETIM

ETIM 3.0	EC001530
ETIM 4.0	EC000217
ETIM 5.0	EC000217
ETIM 6.0	EC001530
ETIM 7.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

Approvals

Approvals

Approvals

CSA / UL Recognized

Ex Approvals

Approval details

CSA		http://www.csagroup.org/services-industries/product-listing/	252259
-----	---	---	--------

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 310982
---------------	---	---	---------------

Accessories

Accessories

Ink ribbon

Shrink sleeve - WMS 25,4 (60X40)R YE - 0800405

Accessories

Ink ribbon - THERMOMARK-RIBBON 110-WMSU - 0801358



Ink ribbon, for roll printer for printing product groups WMS... and WMS-2 HF..., width: 110 mm, color: black

Ink ribbon - THERMOMARK-RIBBON 64-WMSU - 0801360



Ink ribbon, for roll printer for printing product groups WMS... and WMS-2 HF..., width: 64 mm, color: black

Ink ribbon - THERMOMARK-RIBBON 64-WMSU WH - 0801361



Ink ribbon, for roll printer for printing product group WMS... (black), width: 64 mm, color: white

Ink ribbon - THERMOMARK-RIBBON 110-WMSU WH - 0801359



Ink ribbon, for roll printer for printing product group WMS... (black), width: 110 mm, color: white

Printing system accessories

Media hub - THERMOMARK ROLL-ERH - 5146448



External media hub, for the THERMOMARK ROLL, for roll diameter of 150 to 400 mm

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[0800405](#)