

Conductor marking collar - PMH 0:UNBEDRUCKT - 0800417

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Conductor marking collar, yellow: without print, mounting type: thread on, cable diameter range: 1.4 ... 2.5 mm, lettering field size: 3.2 x 2.6 mm

RoHS

Key Commercial Data

Packing unit	100 pc
Minimum order quantity	100 pc
GTIN	 4 017918 005979
GTIN	4017918005979

Technical data

Dimensions

Length (b)	4.5 mm
Width (a)	3.2 mm
Cable diameter	1.4 mm ... 2.5 mm

Ambient conditions

Ambient temperature (operation)	-45 °C ... 70 °C
Ambient temperature (assembly)	> 10 °C

General

Color	yellow
Type	Profile
Components	free from silicone, halogen, and cadmium
Flammability rating according to UL 94	V0
Material	Ethylene-vinyl acetate (EVA)
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Printing	without print
Marking mounting type	thread on
Min. cross section	0.5 mm ²

Conductor marking collar - PMH 0:UNBEDRUCKT - 0800417

Technical data

General

Max. cross section	0.75 mm²
AWG min	20
AWG max	16

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Flammability rating according to UL 94	V0

Classifications

eCl@ss

eCl@ss 10.0.1	27400401
eCl@ss 4.0	27061700
eCl@ss 4.1	27061700
eCl@ss 5.0	27400400
eCl@ss 5.1	27400400
eCl@ss 6.0	27400400
eCl@ss 7.0	27400401
eCl@ss 8.0	27400401
eCl@ss 9.0	27400401

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC001530
ETIM 5.0	EC001530
ETIM 6.0	EC001530
ETIM 7.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

Accessories

Accessories

Conductor marking collar - PMH 0:UNBEDRUCKT - 0800417

Accessories

Assortment box

Range box - SORTI 4/12 - 5020658



Assortment box, 12 compartments external dimensions 335 x 225 x 55 mm, material: Polystyrene

Mounting material

Alignment tool for cable markers - AFD-1 - 0800666



Threading pin, helps thread PMH onto the conductor; insert conductor into pin opening and slide collar on. For external conductor cross section: 2.0 - 2.5 mm

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

0800417