

## Shrink sleeve - WMS 6,4 (15X10)RXL - 0801595

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Shrink sleeve, Roll, white, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL: without print, perforated, mounting type: slide-on, lettering field size: 15 x 10 mm, Number of individual labels: 10000

### Your advantages

- ✓ WMS ... shrink sleeves provide permanent and captive conductor and cable marking
- ✓ The sleeves are pre-assembled for optimum use of material
- ✓ The conductor to be marked is simply threaded through the sleeve and fixed by shrinking the sleeve
- ✓ The sleeves remain flexible after shrinking
- ✓ Up to four markers per sleeve are separated by perforations
- ✓ UL 224 (125°C, 600 V, all tubing)
- ✓ CSA.C22.2 No. 198.1 (125°C, 600 V, all tubing)

**RoHS**

### Key Commercial Data

|              |                                                                                                         |
|--------------|---------------------------------------------------------------------------------------------------------|
| Packing unit | 1 pc                                                                                                    |
| GTIN         | <br>4 046356 676267 |
| GTIN         | 4046356676267                                                                                           |

### Technical data

#### Dimensions

|                |        |
|----------------|--------|
| Length (b)     | 15 mm  |
| Width (a)      | 10 mm  |
| Cable diameter | 6.4 mm |

#### Ambient conditions

|                                |                                                                                                         |
|--------------------------------|---------------------------------------------------------------------------------------------------------|
| Recommended storage conditions | 23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended. |
|--------------------------------|---------------------------------------------------------------------------------------------------------|

#### General

|                       |             |
|-----------------------|-------------|
| Color                 | white       |
| Base element material | polyolefine |

# Shrink sleeve - WMS 6,4 (15X10)RXL - 0801595

## Technical data

### General

|                                                                     |                                     |
|---------------------------------------------------------------------|-------------------------------------|
| Type                                                                | Shrink sleeve                       |
| Components                                                          | halogen-free                        |
| Material                                                            | Polyolefine                         |
| Shrink rate                                                         | 3:1                                 |
| RoHS compliant                                                      | Yes                                 |
| Wipe resistance                                                     | DIN EN 61010-1 (VDE 0411-1)         |
| Printing                                                            | without print                       |
| Number of individual labels                                         | 10000                               |
| Test for substances that would hinder coating with paint or varnish | VW PV 3.10.7:2005-02                |
| Result                                                              | Test passed                         |
| Test specification weathering-resistance                            | Following ISO 4892-2:2013-03        |
| Test duration                                                       | 96 h                                |
| Result of weather resistance test                                   | Test passed                         |
| Salt spray test specification                                       | DIN EN 60068-2-11:2000-02           |
| Test duration                                                       | 96 h                                |
| Salt spray testing result                                           | Test passed                         |
| Wipe resistance of test specification inscriptions                  | DIN EN 61010-1 (VDE 0411-1):2011-07 |
| Result of wipe resistance test                                      | Test passed                         |
| Marking mounting type                                               | slide-on                            |

### Standards and Regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

## Classifications

### eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27400401 |
| eCl@ss 4.1    | 24190200 |
| eCl@ss 5.0    | 27400100 |
| eCl@ss 5.1    | 27400100 |
| eCl@ss 6.0    | 27400100 |
| eCl@ss 7.0    | 27400105 |
| eCl@ss 8.0    | 27400105 |
| eCl@ss 9.0    | 27400401 |

### ETIM

|          |          |
|----------|----------|
| ETIM 4.0 | EC000217 |
| ETIM 5.0 | EC000217 |
| ETIM 6.0 | EC001530 |
| ETIM 7.0 | EC001530 |

## Shrink sleeve - WMS 6,4 (15X10)RXL - 0801595

### Classifications

#### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 13.2 | 39131504 |
| UNSPSC 18.0 | 39131504 |
| UNSPSC 19.0 | 39131504 |
| UNSPSC 20.0 | 39131504 |
| UNSPSC 21.0 | 39131504 |

### Approvals

#### Approvals

##### Approvals

CSA / UL Recognized

##### Ex Approvals

#### Approval details

|     |                                                                                     |                                                                                                                                         |        |
|-----|-------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------|--------|
| CSA |  | <a href="http://www.csagroup.org/services-industries/product-listing/">http://www.csagroup.org/services-industries/product-listing/</a> | 252259 |
|-----|-------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------|--------|

|               |                                                                                     |                                                                                                                                                       |               |
|---------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|
| UL Recognized |  | <a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a> | FILE E 310982 |
|---------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|

### Accessories

#### Accessories

##### Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 64-WMSU - 0801360



Ink ribbon, for roll printer for printing product groups WMS... and WMS-2 HF..., width: 64 mm, color: black

## Shrink sleeve - WMS 6,4 (15X10)RXL - 0801595

### Accessories

Ink ribbon - THERMOMARK-RIBBON 110-WMSU - 0801358



Ink ribbon, for roll printer for printing product groups WMS... and WMS-2 HF..., width: 110 mm, color: black

---

### Printing system accessories

Media hub - THERMOMARK ROLL-ERH - 5146448



External media hub, for the THERMOMARK ROLL, for roll diameter of 150 to 400 mm

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[0801595](#)