

Marker card - SK U/3,8 WH:UNBEDRUCKT - 0803906

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Marker card, Sheet, white, unlabeled, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, Office printing systems, mounting type: adhesive, for terminal block width: 210 mm, lettering field size: 186 x 3.8 mm, Number of individual labels: 1440



Your advantages

- ✓ Labeling service: Phoenix Contact can custom-label SK markers according to your requirements
- ✓ The SK labeling range offers self-adhesive marker strips for labeling products that do not have a marker groove
- ✓ Labeling service: Phoenix Contact can custom-label SK markers according to your requirements
- ✓ Ideal for labeling COMBICON connectors

RoHS

Key Commercial Data

Packing unit	10 pc
GTIN	 4 017918 007799
GTIN	4017918007799

Technical data

Dimensions

Length (b)	186 mm
Width (a)	3.8 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
Ambient temperature (assembly)	> 0 °C
Recommended storage conditions	20-25 °C / 40-50 % relative humidity.

General

Note	Print image may vary depending on laser printer
Color	white
Type	Label
Components	free from silicone and halogen

Marker card - SK U/3,8 WH:UNBEDRUCKT - 0803906

Technical data

General

Material	Polyester
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	1440
Number of individual labels per row	36
Number of marker strips	40
Adhesive	Acrylic
Printability	Office printing systems
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Result of weather resistance test	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result of wipe resistance test	Test passed
Foil strength	50 µm
Adhesive strength	20 µm
Marking mounting type	adhesive

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Classifications

eCl@ss

eCl@ss 10.0.1	27141137
eCl@ss 4.0	24190200
eCl@ss 4.1	24190200
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137
eCl@ss 9.0	27141137

Marker card - SK U/3,8 WH:UNBEDRUCKT - 0803906

Classifications

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761
ETIM 6.0	EC000761
ETIM 7.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131505
UNSPSC 18.0	39131505
UNSPSC 19.0	39131505
UNSPSC 20.0	39131505
UNSPSC 21.0	39131505

Accessories

Accessories

Marker pen

Marker pen - B-STIFT - 1051993



Marker pen, for manual labeling of unprinted Zack strips, smear-proof and waterproof, line thickness 0.5 mm

Marker pen - CMS-PEN 0,25 - 5067815



Marker pen, incl. adapter, ink tank and reservoir, 0.25 mm nib

Marker card - SK U/3,8 WH:UNBEDRUCKT - 0803906

Accessories

Marker pen - CMS-PEN 0,35 - 5067828



Marker pen, incl. adapter, ink tank and reservoir, 0.35 mm nib

Marker pen - CMS-PEN 0,50 - 5067831



Marker pen, incl. adapter, ink tank and reservoir, 0.5 mm nib

Disposable pen, non-refillable - P-PEN - 0815211



Disposable marker pen, non-refillable, for manual marking, can also be used for plotter marking in combination with the P-PEN ADAPTER, line thickness 0.1 mm

Mounting material

Adapter - P-PEN ADAPTER - 0815224



Aluminum adapter, to fix the P-PEN during plotter marking

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[0803906](#)