

Thermal transfer printer - THERMOMARK ROLLMASTER 300 - 0804501

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Thermal transfer printer for material off the roll, incl. Euro/US power cable and USB cable. Support CD includes user manuals in several languages, links to firmware, drivers, and planning and marking software. Operating instructions printed in German and English. 1 roll of labels EML (20x8)R white = 1000 labels, ink ribbon = 50 m

Product Description

The THERMOMARK ROLLMASTER 300 prints markers in roll format for top quality terminal, wire, cable, equipment, and plant marking applications. You can easily create high-quality printed labels and markers.

Your advantages

- ✓ The THERMOMARK ROLLMASTER 300 is an industrial printer for printing large quantities of marking materials in roll format. Print resolution of 300 dpi.
- ✓ Printing of punched and continuous adhesive labels, insert labels, and shrink sleeves
- ✓ Fast, high-quality, and durable printing
- ✓ Easy and intuitive operation via touch color display
- ✓ Easy and intuitive operation via touch color display
- ✓ Easy to control with the PROJECT complete software
- ✓ USB and Ethernet connections

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 381619
GTIN	4055626381619

Technical data

General

Interface	10/100 Mbps Ethernet
	USB 2.0
Weight	10 kg

Dimensions

Length	460 mm
Height	288 mm

Thermal transfer printer - THERMOMARK ROLLMASTER 300 - 0804501

Technical data

Dimensions

Width	252 mm
-------	--------

Connection data

Minimum voltage	100 V AC
Max. voltage	240 V AC

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 10;
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 10.0.1	19140104
eCl@ss 4.0	24190103
eCl@ss 4.1	24190103
eCl@ss 5.0	19020205
eCl@ss 5.1	19020205
eCl@ss 6.0	19140100
eCl@ss 7.0	19140104
eCl@ss 8.0	19140104
eCl@ss 9.0	19140104

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC001694
ETIM 6.0	EC001672
ETIM 7.0	EC001672

UNSPSC

UNSPSC 6.01	43172501
UNSPSC 7.0901	43212107
UNSPSC 11	43172501
UNSPSC 12.01	43212107
UNSPSC 13.2	43212107
UNSPSC 18.0	43212108
UNSPSC 19.0	43212108
UNSPSC 20.0	43212108
UNSPSC 21.0	43212108

Thermal transfer printer - THERMOMARK ROLLMASTER 300 - 0804501

Approvals

Approvals

Approvals

UL Listed / cUL Listed / CCC / EAC / cULus Listed

Ex Approvals

Approval details

UL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 140403
cUL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 140403
CCC			2018010904060718
EAC			RU D- DE.GB09.B.00141
cULus Listed			

Accessories

Accessories

Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 110 - 5145384



Ink ribbon, for roll printers for printing the product groups TML..., WML..., WML HF..., WML-FLAG..., EML..., EML-ESD..., EML-RM..., EML-HA..., EMLS..., EMLC..., EMLP... and PMM..., width: 110 mm, color: black

Thermal transfer printer - THERMOMARK ROLLMASTER 300 - 0804501

Accessories

Ink ribbon - THERMOMARK-RIBBON 110 BU - 0829544



Ink ribbon, width: 110 mm, color: blue

Ink ribbon - THERMOMARK-RIBBON 110 GN - 0829542



Ink ribbon, width: 110 mm, color: green

Ink ribbon - THERMOMARK-RIBBON 110 RD - 0829543



Ink ribbon, width: 110 mm, color: red

Ink ribbon - THERMOMARK-RIBBON 110-EML-HT - 0800342



Ink ribbon, for roll printer for printing product group EML-HT..., width: 110 mm, color: black

Ink ribbon - THERMOMARK-RIBBON 110-WMSU - 0801358



Ink ribbon, for roll printer for printing product groups WMS... and WMS-2 HF..., width: 110 mm, color: black

Thermal transfer printer - THERMOMARK ROLLMASTER 300 - 0804501

Accessories

Ink ribbon - THERMOMARK-RIBBON 110-WMSU WH - 0801359



Ink ribbon, for roll printer for printing product group WMS... (black), width: 110 mm, color: white

Ink ribbon - THERMOMARK-RIBBON 64-WMSU - 0801360



Ink ribbon, for roll printer for printing product groups WMS... and WMS-2 HF..., width: 64 mm, color: black

Ink ribbon - THERMOMARK-RIBBON 64-WMSU WH - 0801361



Ink ribbon, for roll printer for printing product group WMS... (black), width: 64 mm, color: white

Ink ribbon - THERMOMARK-RIBBON 110-WMTB HF - 5148007



Ink ribbon, for roll printer for printing product groups WMTB HF..., WMS-2 HF..., TMT..., and EMT..., width: 110 mm, color: black

Ink ribbon - TM-RIBBON 110-WMTB HF WH - 0802990



Ink ribbon, for roll printer for printing product group WMTB HF..., width: 110 mm, color: white

Thermal transfer printer - THERMOMARK ROLLMASTER 300 - 0804501

Accessories

Ink ribbon - THERMOMARK-RIBBON 25-WMSU - 0803390



Ink ribbon, for roll printer for printing product groups WMS... and WMS-2 HF..., width: 25 mm, color: black

Planning and marking software

Software - CLIP-PROJECT ADVANCED - 5146040



Multilingual software for convenient configuration of Phoenix Contact products on standard DIN rails.

Software - CLIP-PROJECT PROFESSIONAL - 5146053



Multilingual software for terminal strip configuration. A marking module enables the professional marking of markers and labels for identifying terminal blocks, conductors and cables, and devices.

Printing system accessories

Cutter - THERMOMARK ROLLMASTER-CUTTER - 0804502



Cutter, for the THERMOMARK ROLLMASTER 300/600, cutter width: 120 mm, suitable for: TML, SK, EML, RM, PMM, WMS, WMS-2 HF, WMS-OT HF, TMT continuous media, and EMT (EX15)R

Cutter - THERMOMARK ROLLMASTER-CUTTER/P - 0804503



Perforation cutter, for the THERMOMARK ROLLMASTER 300/600, suitable for: WMS, WMS-2 HF, WMS-OT HF, TMT continuous media, and EMT (EX15)R

Thermal transfer printer - THERMOMARK ROLLMASTER 300 - 0804501

Accessories

Screw - TRM-ADAPTER SCREW - 0804653



Adapter screw for using the existing THERMOMARK X1.2 CUTTER and THERMOMARK X1.2 CUTTER/P

Media hub - THERMOMARK ROLL-ERH - 5146448



External media hub, for the THERMOMARK ROLL, for roll diameter of 150 to 400 mm

Media hub - THERMOMARK-ERH 500 - 5146309



External media hub, for the THERMOMARK ROLL, for roll diameter of up to 500 mm

Pressure roller - TRM-PRESSURE ROLLER STANDARD - 0804655



Standard pressure roller

Pressure roller - TRM-PRESSURE ROLLER 4-50 - 0804656



Pressure roller for continuous shrink sleeve

Thermal transfer printer - THERMOMARK ROLLMASTER 300 - 0804501

Accessories

Case - THERMOMARK ROLLMASTER-CASE - 0804643



Transport case for THERMOMARK ROLLMASTER printer

Cleaning pen - CLEANING STICK - 5146697



Cleaning pen

Pressure roller - TRM-MARGIN STOP - 0804657



Pressure roller

Media hub - THERMOMARK ROLL-ERH - 5146448



External media hub, for the THERMOMARK ROLL, for roll diameter of 150 to 400 mm

Media hub - THERMOMARK-ERH 500 - 5146309



External media hub, for the THERMOMARK ROLL, for roll diameter of up to 500 mm

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

0804501