

Printer - BLUEMARK ID - 1003334

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Monochrome printer with UV LED technology, with integrated "MARKING SYSTEM APP" marking software on board. 7" touch color display for printing plastic tags in UC, UCT, US, and UM format, as well as metal plates.

Your advantages

- ✓ The printer detects the direction of the inserted sheets and automatically rotates printing 180° if required
- ✓ Intuitive and time-saving operation using integrated marking software and a graphical user interface
- ✓ Marking that is instantly wipe-resistant, so that marking materials are ready for immediate use
- ✓ Rapid marking of plastic and metal plates for marking terminals, conductors, cables, devices, and plant marking
- ✓ Scalable print resolution between standard (300 dpi) and HD printing (600 dpi)
- ✓ Environmentally-sound, emission-free high-speed printer with modern UV LED technology

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 471075
GTIN	4055626471075

Technical data

General

Interface	10/100 Mbps Ethernet
	1x USB 2.0 Device, 1x USB 2.0 Host
Weight	21 kg

Dimensions

Length	675 mm
Height	340 mm
Width	523 mm

Connection data

Minimum voltage	100 V AC
Max. voltage	240 V AC

Printer - BLUEMARK ID - 1003334

Technical data

Connection data

Additional text	50 Hz ... 60 Hz
-----------------	-----------------

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 10.0.1	19140190
eCl@ss 6.0	19140100
eCl@ss 7.0	19140190
eCl@ss 9.0	19140190

ETIM

ETIM 6.0	EC001672
ETIM 7.0	EC001672

Approvals

Approvals

Approvals

CSA / IECCE CB Scheme / CSAus / EAC-RoHS / EAC / cCSAus

Ex Approvals

Approval details

CSA		http://www.csagroup.org/services-industries/product-listing/	70178753
-----	---	---	----------

IECEE CB Scheme		http://www.iecee.org/	NO102150
-----------------	---	---	----------

Printer - BLUEMARK ID - 1003334

Approvals

CSAus		http://www.csagroup.org/services-industries/product-listing/	70178753
EAC-RoHS			RU D- DE.HB49.B.00023
EAC			RU D- DE.GB09.B.00141
cCSAus			

Accessories

Accessories

Magazine

Magazine - BM ID-ADAPTER PLATE-US - 1044355



Adapter plate for accommodating US sheets

Magazine - BM ID-MAG20 - 1044356



Infeed magazine for accommodating a max. of 20 UniCard sheets

Magazine - BM ID-MAG40 - 1044357



Infeed magazine for accommodating a maxi. of 40 UniCard sheets

Printer - BLUEMARK ID - 1003334

Accessories

Magazine - BLUEMARK MAG EM-M (27X15) - 0802736



Magazine, width: 76 mm, color: white

Magazine - BLUEMARK MAG EM-M (27X18) - 0802737



Magazine, width: 76 mm, color: white

Magazine - BLUEMARK MAG EM-M (49X15) - 0802738



Magazine, width: 76 mm, color: white

Magazine - BLUEMARK MAG EM-M (60X15) - 0802739



Magazine, width: 76 mm, color: white

Magazine - BLUEMARK MAG EM-M (60X30) - 0802740



Magazine, width: 76 mm, color: white

Printer - BLUEMARK ID - 1003334

Accessories

Magazine - BLUEMARK MAG EM-M (85,6X54) - 0802741



Magazine, width: 76 mm, color: white

Magazine - BLUEMARK MAG EM-M (100X60) - 0802742



Magazine, width: 76 mm, color: white

Magazine - BLUEMARK MAG WM-M (29X8) - 0802743



Magazine, width: 76 mm, color: white

Magazine - BLUEMARK MAG WM-M (40X15) - 0802744



Magazine, width: 76 mm, color: white

Magazine - BLUEMARK MAG WM-M (60X15) - 0802746



Magazine, width: 76 mm, color: white

Printer - BLUEMARK ID - 1003334

Accessories

Magazine - BLUEMARK MAG WM-M (D30) - 0802747



Magazine, width: 76 mm, color: white

Magazine - BLUEMARK MAG AI-WM - 5146567



Magazine for BLUEMARK printer, for accommodating 0.5 - 1.5 mm² ferrules with insulating collar that can be labeled

Magazine - BLUEMARK MAG AI-WM 2,5 - 5146640



Magazine for BLUEMARK printer, for accommodating 2.5 mm² ferrules with insulating collar that can be labeled

Magazine - BLUEMARK MAG ZB - 5146529

Magazine for BLUEMARK, only for ZB 7,62 UV-100 - 0829029

Magazine - BLUEMARK MAG ZB 8/27 - 5146558



Magazine for BLUEMARK, only for ZB 8/27 UV-100 - 0829102

Magazine - BLUEMARK MAG BN-ZB - 5146192



Magazine

Printer - BLUEMARK ID - 1003334

Accessories

Printing system accessories

Ink cartridge - BM ID-CARTR. BK - 1044345



Replacement UV fluid, 23 ml, color: black

Ink cartridge - BM ID-DUMMY CARTR. BK - 1044351



Dummy cartridge for transportation, color: black

Original packaging - BM ID-CARDBOARD BOX - 1044361



Original packaging for transportation

Cleaning cartridge - BM ID-CLEANING CARTR. - 1044350



Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1003334](#)