

Warning label - US-PML-W100 (25X25) - 1014125

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Warning label, Card, yellow/black, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: adhesive, diameter: 0 mm, lettering field size: 25 x 25 mm, Number of individual labels: 24



Your advantages

- UniSheet - stick-on warning labels, unmarked
- Suitable for indoor and outdoor use
- The warning labels conform to the ISO 7010 international standard
- Highly flexible, plasticized PVC labels which are ideal for uneven surfaces



Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	
GTIN	4046356786386

Technical data

Dimensions

Length (b)	25 mm
Width (a)	25 mm
Height (c)	21.65 mm
Diameter	0.00 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 90 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.

General

Color	yellow/black
Type	Triangle

Warning label - US-PML-W100 (25X25) - 1014125

Technical data

General

Components	Silicone-free
Material	PVC
RoHS compliant	Yes
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	24
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Result of weather resistance test	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result of wipe resistance test	Test passed
Foil strength	50 µm
Marking mounting type	adhesive

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Classifications

eCl@ss

eCl@ss 10.0.1	40200202
eCl@ss 4.0	40200100
eCl@ss 4.1	40200100
eCl@ss 5.0	40200100
eCl@ss 5.1	27371300
eCl@ss 6.0	40200100
eCl@ss 7.0	40200103
eCl@ss 8.0	40200202
eCl@ss 9.0	40200202

ETIM

ETIM 3.0	EC000712
ETIM 4.0	EC001777
ETIM 5.0	EC001777
ETIM 6.0	EC001777
ETIM 7.0	EC001777

Warning label - US-PML-W100 (25X25) - 1014125

Classifications

UNSPSC

UNSPSC 6.01	43172501
UNSPSC 7.0901	43212107
UNSPSC 11	43172501
UNSPSC 12.01	43212107
UNSPSC 13.2	55121718
UNSPSC 18.0	55121718
UNSPSC 19.0	55121718
UNSPSC 20.0	55121718
UNSPSC 21.0	55121718

Accessories

Accessories

Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 110-TC - 0801371



Ink ribbon, for THERMOMARK CARD for printing product groups UCT..., US..., and UM..., width: 110 mm, color: black

Magazine

Magazine - TMP-US-MAG1 - 0803341



Magazine, For THERMOMARK CARD and THERMOMARK PRIME, for accommodating US cards

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1014125](#)