

Pipeline markers - PML-T106 (52X560)R - 1014240

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Pipeline markers, Roll, orange, pre-printed, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 52 x 560 mm, Number of individual labels: 250



Your advantages

- ✓ Stick-on pipeline markers, unmarked
- ✓ Suitable for indoor and outdoor use
- ✓ Pipeline marking according to DIN 2403
- ✓ In combination with the PML-GHS hazardous substances labels, marking which conforms to the Ordinance on Hazardous Substances (GefStoffV) can be applied
- ✓ High adhesive strength
- ✓ Finely perforated arrowheads enable the arrowheads which are not required to be easily removed
- ✓ High temperature resistance
- ✓ Group 6 (acids)
- ✓ External media hub, for the THERMOMARK ROLL, for roll diameter of up to 500 mm

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 784368
GTIN	4046356784368

Technical data

Dimensions

Length (b)	52 mm
Width (a)	560 mm
Height (c)	52 mm
Diameter	0.00 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
---------------------------------	-------------------

Pipeline markers - PML-T106 (52X560)R - 1014240

Technical data

General

Note	This item may only be used with the THERMOMARK ROLL X1 or an external media hub.
Color	orange
Type	Rectangle
Components	Silicone-free
Material	Polyester
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	250
Marking mounting type	adhesive

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Classifications

eCl@ss

eCl@ss 10.0.1	40200202
eCl@ss 4.0	27141100
eCl@ss 4.1	27141100
eCl@ss 5.0	27149100
eCl@ss 5.1	27371300
eCl@ss 6.0	27149100
eCl@ss 7.0	27149129
eCl@ss 8.0	40200202
eCl@ss 9.0	40200202

ETIM

ETIM 3.0	EC000712
ETIM 4.0	EC002498
ETIM 5.0	EC001288
ETIM 6.0	EC001288
ETIM 7.0	EC001288

UNSPSC

UNSPSC 6.01	43172501
UNSPSC 7.0901	43212107
UNSPSC 11	43172501
UNSPSC 12.01	43212107
UNSPSC 13.2	39131504
UNSPSC 18.0	55121718
UNSPSC 19.0	55121718
UNSPSC 20.0	55121718

Pipeline markers - PML-T106 (52X560)R - 1014240

Classifications

UNSPSC

UNSPSC 21.0	55121718
-------------	----------

Accessories

Accessories

Ink ribbon

Ink ribbon - TM-RIBBON 110 WH 101 - 1099966



Ink ribbon, For THERMOMARK roll printers for printing the product group material off the roll: PML-T..., width: 110 mm, color: white

Printing system accessories

Media hub - THERMOMARK ROLL-ERH - 5146448



External media hub, for the THERMOMARK ROLL, for roll diameter of 150 to 400 mm

Warning label printed

Hazardous substances label - PML-GHS102 (25X25) - 1014272



Hazardous substances label, Sheet, red/white, labeled: Flammable, mounting type: adhesive, diameter: 0 mm, lettering field size: 25 x 25 mm, Number of individual labels: 4

Hazardous substances label - PML-GHS103 (25X25) - 1014274



Hazardous substances label, Sheet, red/white, labeled: Oxidizing, mounting type: adhesive, diameter: 0 mm, lettering field size: 25 x 25 mm, Number of individual labels: 4

Pipeline markers - PML-T106 (52X560)R - 1014240

Accessories

Hazardous substances label - PML-GHS105 (13X13) - 1014277



Hazardous substances label, Sheet, red/white, labeled: Corrosive, mounting type: adhesive, diameter: 0 mm, lettering field size: 13 x 13 mm, Number of individual labels: 35

Hazardous substances label - PML-GHS105 (25X25) - 1014278



Hazardous substances label, Sheet, red/white, labeled: Corrosive, mounting type: adhesive, diameter: 0 mm, lettering field size: 25 x 25 mm, Number of individual labels: 4

Hazardous substances label - PML-GHS106 (25X25) - 1014280



Hazardous substances label, Sheet, red/white, labeled: Toxic, mounting type: adhesive, diameter: 0 mm, lettering field size: 25 x 25 mm, Number of individual labels: 9

Hazardous substances label - PML-GHS107 (25X25) - 1014282



Hazardous substances label, Sheet, red/white, labeled: Irritant, mounting type: adhesive, diameter: 0 mm, lettering field size: 25 x 25 mm, Number of individual labels: 9

Hazardous substances label - PML-GHS109 (13X13) - 1014285



Hazardous substances label, Sheet, red/white, labeled: Hazardous to the environment, mounting type: adhesive, diameter: 0 mm, lettering field size: 13 x 13 mm, Number of individual labels: 35

Pipeline markers - PML-T106 (52X560)R - 1014240

Accessories

Hazardous substances label - PML-GHS109 (25X25) - 1014286



Hazardous substances label, Sheet, red/white, labeled: Hazardous to the environment, mounting type: adhesive, diameter: 0 mm, lettering field size: 25 x 25 mm, Number of individual labels: 9

Warning label unprinted

Hazardous substances label - US-PML-GHS100 (13X13) - 1014287



Hazardous substances label, Card, red/white, pre-printed, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: adhesive, diameter: 0 mm, lettering field size: 13 x 13 mm, Number of individual labels: 50

Hazardous substances label - US-PML-GHS100 (25X25) - 1014288



Hazardous substances label, Card, red/white, pre-printed, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: adhesive, diameter: 0 mm, lettering field size: 25 x 25 mm, Number of individual labels: 9

Hazardous substances label - PML-GHS100 (13X13)R - 1014289



Hazardous substances label, Roll, white/red, pre-printed, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 13 x 13 mm, Number of individual labels: 500

Hazardous substances label - PML-GHS100 (25X25)R - 1014290



Hazardous substances label, Roll, white/red, pre-printed, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 25 x 25 mm, Number of individual labels: 500

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1014240](#)