

Pipeline markers - PML-T105 (52X560)R CUS - 1014258

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Pipeline markers, can be ordered: by line, yellow/black, labeled according to customer specifications: Non-flammable liquids, mounting type: adhesive, diameter: 0 mm, lettering field size: 52 x 560 mm



Your advantages

- ☒ Group 5 (non-combustible gases)



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 784542
GTIN	4046356784542

Technical data

Dimensions

Length (b)	52 mm
Width (a)	560 mm
Height (c)	52 mm
Diameter	0.00 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
---------------------------------	-------------------

General

Color	yellow/black
Type	Rectangle
Components	Silicone-free
Material	Polyester
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Printing	Non-flammable liquids
Number of individual labels per row	1

Pipeline markers - PML-T105 (52X560)R CUS - 1014258

Technical data

General

Marking mounting type	adhesive
-----------------------	----------

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Classifications

eCl@ss

eCl@ss 10.0.1	40200202
eCl@ss 4.0	40200100
eCl@ss 4.1	40200100
eCl@ss 5.0	40200100
eCl@ss 5.1	27371300
eCl@ss 6.0	40200100
eCl@ss 7.0	40200103
eCl@ss 8.0	40200202
eCl@ss 9.0	40200202

ETIM

ETIM 3.0	EC000712
ETIM 4.0	EC002498
ETIM 5.0	EC001777
ETIM 6.0	EC001777
ETIM 7.0	EC001777

UNSPSC

UNSPSC 6.01	43172501
UNSPSC 7.0901	43212107
UNSPSC 11	43172501
UNSPSC 12.01	43212107
UNSPSC 13.2	55121718
UNSPSC 18.0	55121718
UNSPSC 19.0	55121718
UNSPSC 20.0	55121718
UNSPSC 21.0	55121718

Accessories

Accessories

Ink ribbon

Pipeline markers - PML-T105 (52X560)R CUS - 1014258

Accessories

Ink ribbon - TM-RIBBON 110 WH 101 - 1099966



Ink ribbon, For THERMOMARK roll printers for printing the product group material off the roll: PML-T..., width: 110 mm, color: white

Warning label printed

Hazardous substances label - PML-GHS102 (25X25) - 1014272



Hazardous substances label, Sheet, red/white, labeled: Flammable, mounting type: adhesive, diameter: 0 mm, lettering field size: 25 x 25 mm, Number of individual labels: 4

Hazardous substances label - PML-GHS103 (25X25) - 1014274



Hazardous substances label, Sheet, red/white, labeled: Oxidizing, mounting type: adhesive, diameter: 0 mm, lettering field size: 25 x 25 mm, Number of individual labels: 4

Hazardous substances label - PML-GHS105 (13X13) - 1014277



Hazardous substances label, Sheet, red/white, labeled: Corrosive, mounting type: adhesive, diameter: 0 mm, lettering field size: 13 x 13 mm, Number of individual labels: 35

Hazardous substances label - PML-GHS105 (25X25) - 1014278



Hazardous substances label, Sheet, red/white, labeled: Corrosive, mounting type: adhesive, diameter: 0 mm, lettering field size: 25 x 25 mm, Number of individual labels: 4

Pipeline markers - PML-T105 (52X560)R CUS - 1014258

Accessories

Hazardous substances label - PML-GHS106 (25X25) - 1014280



Hazardous substances label, Sheet, red/white, labeled: Toxic, mounting type: adhesive, diameter: 0 mm, lettering field size: 25 x 25 mm, Number of individual labels: 9

Hazardous substances label - PML-GHS107 (25X25) - 1014282



Hazardous substances label, Sheet, red/white, labeled: Irritant, mounting type: adhesive, diameter: 0 mm, lettering field size: 25 x 25 mm, Number of individual labels: 9

Hazardous substances label - PML-GHS109 (13X13) - 1014285



Hazardous substances label, Sheet, red/white, labeled: Hazardous to the environment, mounting type: adhesive, diameter: 0 mm, lettering field size: 13 x 13 mm, Number of individual labels: 35

Hazardous substances label - PML-GHS109 (25X25) - 1014286



Hazardous substances label, Sheet, red/white, labeled: Hazardous to the environment, mounting type: adhesive, diameter: 0 mm, lettering field size: 25 x 25 mm, Number of individual labels: 9

Warning label unprinted

Hazardous substances label - US-PML-GHS100 (13X13) - 1014287



Hazardous substances label, Card, red/white, pre-printed, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: adhesive, diameter: 0 mm, lettering field size: 13 x 13 mm, Number of individual labels: 50

Pipeline markers - PML-T105 (52X560)R CUS - 1014258

Accessories

Hazardous substances label - US-PML-GHS100 (25X25) - 1014288



Hazardous substances label, Card, red/white, pre-printed, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: adhesive, diameter: 0 mm, lettering field size: 25 x 25 mm, Number of individual labels: 9

Hazardous substances label - PML-GHS100 (13X13)R - 1014289



Hazardous substances label, Roll, white/red, pre-printed, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 13 x 13 mm, Number of individual labels: 500

Hazardous substances label - PML-GHS100 (25X25)R - 1014290



Hazardous substances label, Roll, white/red, pre-printed, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 25 x 25 mm, Number of individual labels: 500

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

1014258