

## Magnetic label - PMM (EX30)R SR - 1014310

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Magnetic label, Roll, silver, unlabeled, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: magnetic adhesion, lettering field size: 15000 x 30 mm, Number of individual labels: 1

### Your advantages

- ✓ Magnetic labels, unprinted
- ✓ The magnetic labels supplied in rolls represent an individual and flexible marking solution, e.g., for warehouse marking.
- ✓ High adhesive strength
- ✓ The flexible magnetic tape will also adhere to round objects with a radius from 12 mm
- ✓ Magnetic tape coated with polyester foil

RoHS

### Key Commercial Data

|              |                                                                                                         |
|--------------|---------------------------------------------------------------------------------------------------------|
| Packing unit | 1 pc                                                                                                    |
| GTIN         | <br>4 046356 786140 |
| GTIN         | 4046356786140                                                                                           |

### Technical data

#### Dimensions

|            |          |
|------------|----------|
| Length (b) | 15000 mm |
| Width (a)  | 30 mm    |

#### Ambient conditions

|                                 |                  |
|---------------------------------|------------------|
| Ambient temperature (operation) | -30 °C ... 55 °C |
|---------------------------------|------------------|

#### General

|                                     |                             |
|-------------------------------------|-----------------------------|
| Color                               | silver                      |
| Material                            | Magnetic tape               |
| Coating                             | Polyester foil              |
| Wipe resistance                     | DIN EN 61010-1 (VDE 0411-1) |
| Number of individual labels         | 1                           |
| Number of individual labels per row | 1                           |

# Magnetic label - PMM (EX30)R SR - 1014310

## Technical data

### General

|                       |                   |
|-----------------------|-------------------|
| Marking mounting type | magnetic adhesion |
|-----------------------|-------------------|

### Standards and Regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

## Classifications

### eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27400629 |
| eCl@ss 4.0    | 27141100 |
| eCl@ss 4.1    | 27141100 |
| eCl@ss 5.0    | 27149100 |
| eCl@ss 5.1    | 27371300 |
| eCl@ss 6.0    | 27149100 |
| eCl@ss 7.0    | 27149129 |
| eCl@ss 8.0    | 27149129 |
| eCl@ss 9.0    | 27400629 |

### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC000712 |
| ETIM 4.0 | EC002498 |
| ETIM 5.0 | EC001288 |
| ETIM 6.0 | EC001288 |
| ETIM 7.0 | EC001288 |

### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 43172501 |
| UNSPSC 7.0901 | 43212107 |
| UNSPSC 11     | 43172501 |
| UNSPSC 12.01  | 43212107 |
| UNSPSC 13.2   | 39131504 |
| UNSPSC 18.0   | 39131504 |
| UNSPSC 19.0   | 39131504 |
| UNSPSC 20.0   | 39131504 |
| UNSPSC 21.0   | 39131504 |

## Accessories

### Accessories

#### Ink ribbon

## Magnetic label - PMM (EX30)R SR - 1014310

### Accessories

Ink ribbon - THERMOMARK-RIBBON 110 - 5145384



Ink ribbon, for roll printers for printing the product groups TML..., WML..., WML HF..., WML-FLAG..., EML..., EML-ESD..., EML-RM..., EML-HA..., EMLS..., EMLC..., EMLP... and PMM..., width: 110 mm, color: black

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1014310](#)