

Magnetic label - PMM (EX20)R SR CUS - 1014319

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Magnetic label, can be ordered: by line, silver, labeled according to customer specifications, mounting type: magnetic adhesion, lettering field size: 15000 x 20 mm, Number of individual labels: 1



PRINTED
FOR YOU

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 786232
GTIN	4046356786232

Technical data

Dimensions

Length (b)	15000 mm
Width (a)	20 mm

Ambient conditions

Ambient temperature (operation)	-30 °C ... 55 °C
---------------------------------	------------------

General

Color	silver
Material	Magnetic tape
Coating	Polyester foil
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	1
Number of individual labels per row	1
Marking mounting type	magnetic adhesion

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Magnetic label - PMM (EX20)R SR CUS - 1014319

Classifications

eCl@ss

eCl@ss 10.0.1	27400629
eCl@ss 4.0	40200100
eCl@ss 4.1	40200100
eCl@ss 5.0	40200100
eCl@ss 5.1	27371300
eCl@ss 6.0	40200100
eCl@ss 7.0	40200103
eCl@ss 8.0	40200103
eCl@ss 9.0	27400629

ETIM

ETIM 3.0	EC000712
ETIM 4.0	EC002498
ETIM 5.0	EC001777
ETIM 6.0	EC001288
ETIM 7.0	EC001288

UNSPSC

UNSPSC 6.01	43172501
UNSPSC 7.0901	43212107
UNSPSC 11	43172501
UNSPSC 12.01	43212107
UNSPSC 13.2	55121718
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1014319](#)