

Touch panel - BTP 2102W - 1046667

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Touch panel with 25.9 cm / 10.2" TFT-display (analog resistive (polyester)), 800 x 480 pixel(s) (WVGA), 262144 colors, Arm9™ i.MX28, 454 MHz, 2x COM (RS-232/422/485), 1x USB 2.0, Typ A, 1x USB 2.0, Typ B, 1 x Ethernet (10/100 Mbps), RJ45, Windows® CE 6.0 and user software: Visu+. (bus system: without)

Similar figure

Your advantages

- ✓ Visu+ RT integrated as standard in all BTP 2000 devices
- ✓ Connection to all relevant control systems, thanks to a large number of available drivers
- ✓ Developed for basic applications with attractive price/performance ratio
- ✓ 3 display sizes in 16:9 format

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 644103
GTIN	4055626644103

Technical data

Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Dimensions

Outer dimensions: width, height, depth	268 mm x 190 mm x 5 mm (Dimensions of the front plate)
Installation dimensions: width, height, depth	256 mm x 178 mm x 33 mm (Installation cutout)

Display

Display type	25.9 cm / 10.2" TFT
Screen resolution	800 x 480 Pixel(s) (WVGA)
Touch technology	analog resistive (polyester)
Brightness	300 cd/m², typical (adjustable)
Backlighting	LED

Touch panel - BTP 2102W - 1046667

Technical data

Display

Display backlight MTBF	20000 h
Colors	262144 colors
Reading angle left	65 °
Reading angle right	65 °
Reading angle top	45 °
Reading angle bottom	65 °

Computer data

Processor	Arm9™ i.MX28, 454 MHz
Operating system	Windows® CE 6.0
User software	Visu+
RAM	128 MB DDR2 SDRAM
Mass storage	Flash, 512 MB
Network	1 x Ethernet (10/100 Mbps), RJ45
Interfaces	2x COM (RS-232/422/485)
	1x USB 2.0, Typ A
	1x USB 2.0, Typ B
Bus system	without
Slots	1x SD

General

Housing material	Plastic
Mounting type	Front installation
Weight	900 g

Ambient conditions

Degree of protection	IP66 (on the front), IP20 (on the back)
Ambient temperature (operation)	0 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 85 °C
Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 95 % (non-condensing)
Vibration (operation)	DIN EN 60068-2-6
Shock	DIN EN 60068-2-27

Device supply

Typical current consumption	0.3 A
Power supply unit	24 V DC ±15 %

Standards and Regulations

Shock	DIN EN 60068-2-27
Vibration (operation)	DIN EN 60068-2-6

Environmental Product Compliance

Touch panel - BTP 2102W - 1046667

Technical data

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Classifications

eCl@ss

eCl@ss 10.0.1	27330201
eCl@ss 4.0	27330200
eCl@ss 4.1	27330200
eCl@ss 5.0	27330200
eCl@ss 5.1	27330200
eCl@ss 6.0	27242300
eCl@ss 7.0	27242302
eCl@ss 8.0	27242302
eCl@ss 9.0	27330201

ETIM

ETIM 4.0	EC001412
ETIM 5.0	EC001412
ETIM 6.0	EC001412
ETIM 7.0	EC001412

Approvals

Approvals

Approvals

EAC-RoHS / EAC

Ex Approvals

UL Listed / cUL Listed / cULus Listed

Approval details

EAC-RoHS		RU*- DE*35.B.00394/20
----------	---	--------------------------

EAC		RU C- DE.A*08.B01708
-----	---	-------------------------

Touch panel - BTP 2102W - 1046667

Accessories

Accessories

Data plug

D-SUB gender changer - VS-09-GC-ST/ST - 1652651



D-SUB contact insert, shell size 1, with nine signal contacts, type of contact pin, gender changer, fixing with 4-40 UNC thread

Operating stylus

Touch pen - TOUCH PEN - 2701379



Touch pen for analog-resistive HMI, silver coated. Delivery includes self-adhesive pen holder.

PCB plug

Printed-circuit board connector - MSTB 2,5/ 3-STF-5,08 - 1777992



PCB connector, nominal current: 12 A, rated voltage (III/2): 320 V, nominal cross section: 2.5 mm², number of positions: 3, pitch: 5.08 mm, connection method: Screw connection with tension sleeve, color: green, contact surface: Tin

Storage medium

USB memory stick - USB FLASH DRIVE - 2402809



USB memory stick, 8 GB

Memory - MICROSDHC-16GB - 1154696



Industrial grade 16 GB MicroSDHC 3DTLC

Touch panel - BTP 2102W - 1046667

Accessories

Memory - MICROSDHC-32GB - 1154699



Industrial grade 32 GB MicroSDHC 3DTLC

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

1046667