

Crimping pliers - CRIMPFOX 10S - 1212045

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Crimping pliers, for ferrules without insulating collar according to DIN 46228 Part 1 and ferrules with insulating collar according to DIN 46228 Part 4, 0.14 mm² ... 10 mm², unlockable pressure lock, lateral entry

Your advantages

- ✓ These compact crimping pliers have been designed to reduce effort when working
- ✓ The way in which the handles and the die are arranged means that the ferrules can be fitted however the tool is held



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 455732
GTIN	4046356455732

Technical data

Dimensions

Length (b)	175 mm
------------	--------

General

Color	black
Compression	Square crimp
Type of contact	Insulated and uninsulated ferrules
Designation	Crimping position 1
Min. cross section	0.14 mm ²
Max. cross section	10 mm ²
AWG min	25
AWG max	7
Weight	380 g
Min. cross section	0.14 mm ²
Max. cross section	10 mm ²
AWG min	25
AWG max	7

Environmental Product Compliance

Crimping pliers - CRIMPFOX 10S - 1212045

Technical data

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Classifications

eCl@ss

eCl@ss 10.0.1	21043811
eCl@ss 4.0	21040300
eCl@ss 4.1	21040300
eCl@ss 5.0	21040300
eCl@ss 5.1	21040300
eCl@ss 6.0	21043800
eCl@ss 7.0	21043811
eCl@ss 8.0	21043811
eCl@ss 9.0	21043811

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001186
ETIM 5.0	EC000168
ETIM 6.0	EC000168
ETIM 7.0	EC000168

UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518
UNSPSC 18.0	27111518
UNSPSC 19.0	27111518
UNSPSC 20.0	27111518
UNSPSC 21.0	27111518

Approvals

Approvals

Approvals

EAC

Crimping pliers - CRIMPFOX 10S - 1212045

Approvals

Ex Approvals

Approval details

EAC



RU x-
DE.xx08.B.02974

Accessories

Accessories

Mounting material

Replacement spring - CRIMPFOX/SPR-2 - 1212047



Spare recuperating spring

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1212045](#)