

## Replacement die - CRIMPFOX-M CX-2/DIE - 1212088

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid  
(<http://phoenixcontact.com/download>)



Die, for Crimpfox-M, for coaxial connectors (BNC/TNC) RG 58/ 59/ 62/ 71, packed in a serial storage box

### Key Commercial Data

|              |                                                                                    |
|--------------|------------------------------------------------------------------------------------|
| Packing unit | 1 pc                                                                               |
| GTIN         |  |
| GTIN         | 4046356454483                                                                      |

### Technical data

#### Dimensions

|            |         |
|------------|---------|
| Length (b) | 114 mm  |
| Width (a)  | 75 mm   |
| Height (c) | 25.5 mm |

#### General

|                    |                      |
|--------------------|----------------------|
| Color              | black                |
| Compression        | HEX crimp            |
| Type of contact    | Coaxial connectors   |
| Max. cross section | 1.69 mm <sup>2</sup> |
| Min. cross section | 5.41 mm <sup>2</sup> |
| Max. cross section | 6.48 mm <sup>2</sup> |
| Weight             | 79 g                 |
| Min. cross section | 0 mm <sup>2</sup>    |

### Classifications

#### eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 21019290 |
| eCl@ss 4.0    | 21040300 |
| eCl@ss 4.1    | 21040300 |
| eCl@ss 5.0    | 21040300 |
| eCl@ss 5.1    | 21040300 |

## Replacement die - CRIMPFOX-M CX-2/DIE - 1212088

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 6.0 | 21043800 |
| eCl@ss 7.0 | 21043811 |
| eCl@ss 8.0 | 21043811 |
| eCl@ss 9.0 | 21019290 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC001186 |
| ETIM 3.0 | EC001186 |
| ETIM 4.0 | EC001282 |
| ETIM 5.0 | EC001282 |
| ETIM 6.0 | EC001282 |
| ETIM 7.0 | EC001282 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 27112118 |
| UNSPSC 7.0901 | 27111518 |
| UNSPSC 11     | 23171604 |
| UNSPSC 12.01  | 27111518 |
| UNSPSC 13.2   | 27111518 |
| UNSPSC 19.0   | 27111518 |

### Approvals

#### Approvals

#### Approvals

#### EAC

#### Ex Approvals

#### Approval details

|     |                                                                                     |                          |
|-----|-------------------------------------------------------------------------------------|--------------------------|
| EAC |  | RU x-<br>DE.xx08.B.02974 |
|-----|-------------------------------------------------------------------------------------|--------------------------|

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1212088](#)