

## Sensor/actuator cable - SAC-HZ-3P-2,0-542/ FR SCO BK - 1409537

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Sensor/actuator cable, 3-position, PVC, yellow, free cable end, on Socket angled M12 SPEEDCON, coding: A, cable length: 2 m



### Key Commercial Data

|                        |                                                                                                         |
|------------------------|---------------------------------------------------------------------------------------------------------|
| Packing unit           | 1 pc                                                                                                    |
| Minimum order quantity | 10 pc                                                                                                   |
| GTIN                   | <br>4 055626 017938 |
| GTIN                   | 4055626017938                                                                                           |

### Technical data

#### Dimensions

|                 |     |
|-----------------|-----|
| Length of cable | 2 m |
|-----------------|-----|

#### Ambient conditions

|                                 |                                  |
|---------------------------------|----------------------------------|
| Ambient temperature (operation) | -25 °C ... 90 °C (Plug / socket) |
| Degree of protection            | IP65                             |
|                                 | IP67                             |
|                                 | IP68                             |

#### General

|                       |                                                                                                     |
|-----------------------|-----------------------------------------------------------------------------------------------------|
| Note                  | These cable assemblies are UL/cUL listed for use in Class I, Division 2 (CID2) hazardous locations. |
| Rated current at 40°C | 4 A                                                                                                 |
| Rated voltage         | 250 V AC                                                                                            |
|                       | 250 V DC                                                                                            |
| Number of positions   | 3                                                                                                   |
| Insulation resistance | ≥ 100 MΩ                                                                                            |
| Coding                | A - standard                                                                                        |
| Standards/regulations | M12 connector IEC 61076-2-101                                                                       |

## Sensor/actuator cable - SAC-HZ-3P-2,0-542/ FR SCO BK - 1409537

### Technical data

#### General

|                              |                        |
|------------------------------|------------------------|
| Status display               | No                     |
| Protective circuit/component | unwired                |
| Overvoltage category         | II                     |
| Degree of pollution          | 3                      |
| Torque                       | 0.4 Nm (M12 connector) |

#### Material

|                                        |                                             |
|----------------------------------------|---------------------------------------------|
| Flammability rating according to UL 94 | HB                                          |
| Contact material                       | CuSn                                        |
| Contact surface material               | Ni/Au                                       |
| Contact carrier material               | TPU GF                                      |
| Material of grip body                  | TPU, hardly inflammable, self-extinguishing |
| Material, knurls                       | Zinc die-cast, nickel-plated                |
| Sealing material                       | NBR                                         |

#### Standards and Regulations

|                                        |                                    |
|----------------------------------------|------------------------------------|
| Standards/specifications               | M12 connector IEC 61076-2-101      |
| Flammability rating according to UL 94 | HB                                 |
| UL, USA/Canada                         | Class I, Div. 2, Groups A, B, C, D |

#### Cable

|                                               |                           |
|-----------------------------------------------|---------------------------|
| Cable type                                    | PVC yellow 105 °C         |
| Cable type (abbreviation)                     | 542                       |
| UL AWM style                                  | 2517 (105 °C / 300 V)     |
| AWG signal line                               | 22                        |
| Conductor structure signal line               | 30x 1.30 mm               |
| Core diameter including insulation            | 1.27 mm ±0.03 mm          |
| Wire colors                                   | brown, blue, black        |
| Overall twist                                 | 3 wires, twisted          |
| External sheath, color                        | yellow                    |
| External cable diameter D                     | 4.7 mm ±0.2 mm            |
| Minimum bending radius, flexible installation | 8 x D                     |
| Cable weight                                  | 30 kg/km                  |
| Outer sheath, material                        | PVC                       |
| Material conductor insulation                 | PVC                       |
| Conductor material                            | Tin-plated Cu litz wires  |
| Insulation resistance                         | ≥ (550 M Ohms/m @ 500V)   |
| Conductor resistance                          | max. 50.5 Ω/km (20 °C)    |
| Nominal voltage, cable                        | 300 V                     |
| Special properties                            | UL standards PLTC and ITC |
| Flame resistance                              | FT4                       |
| Other resistance                              | UV resistant              |

## Sensor/actuator cable - SAC-HZ-3P-2,0-542/ FR SCO BK - 1409537

### Technical data

#### Cable


|                                 |                                                 |
|---------------------------------|-------------------------------------------------|
| Ambient temperature (operation) | -30 °C ... 105 °C (cable, fixed installation)   |
|                                 | -5 °C ... 105 °C (cable, flexible installation) |

#### Environmental Product Compliance

|            |                                                         |
|------------|---------------------------------------------------------|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
|            | No hazardous substances above threshold values          |

### Drawings


Dimensional drawing




EXCLIP socket

## Sensor/actuator cable - SAC-HZ-3P-2,0-542/ FR SCO BK - 1409537

Dimensional drawing




EXCLIP mounted plug




## Sensor/actuator cable - SAC-HZ-3P-2,0-542/ FR SCO BK - 1409537

Dimensional drawing



M12 x 1 socket, angled


Circuit diagram



Contact assignment of the M12 socket

## Sensor/actuator cable - SAC-HZ-3P-2,0-542/ FR SCO BK - 1409537


Schematic diagram



Pin assignment M12 socket, 3-pos., A-coded, view female side

## Sensor/actuator cable - SAC-HZ-3P-2,0-542/ FR SCO BK - 1409537

Cable cross section



PVC yellow 105 °C [542]

### Classifications

eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27060311 |
| eCl@ss 4.0    | 27060300 |
| eCl@ss 4.1    | 27060300 |
| eCl@ss 5.0    | 27061800 |
| eCl@ss 5.1    | 27061800 |
| eCl@ss 6.0    | 27279200 |
| eCl@ss 7.0    | 27279218 |
| eCl@ss 8.0    | 27279218 |
| eCl@ss 9.0    | 27060311 |

## Sensor/actuator cable - SAC-HZ-3P-2,0-542/ FR SCO BK - 1409537

### Classifications

#### ETIM

|          |          |
|----------|----------|
| ETIM 4.0 | EC001855 |
| ETIM 5.0 | EC001855 |
| ETIM 6.0 | EC001855 |
| ETIM 7.0 | EC001855 |

#### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 13.2 | 31251501 |
| UNSPSC 19.0 | 31251501 |
| UNSPSC 20.0 | 31251501 |
| UNSPSC 21.0 | 31251501 |

### Approvals

#### Approvals

Approvals

EAC-RoHS

Ex Approvals

UL Listed / cUL Listed / cULus Listed

#### Approval details

|          |                                                                                     |                          |
|----------|-------------------------------------------------------------------------------------|--------------------------|
| EAC-RoHS |  | RU D-<br>DE.HB35.B.00387 |
|----------|-------------------------------------------------------------------------------------|--------------------------|

### Accessories

#### Accessories

Plug for cable screw gland

Screw plug - PROT-M12 MS-PA-CHAIN - 1430899

M12 sealing cap with fixing band, for sensor cables, for free M12 sockets



Protective cap

## Sensor/actuator cable - SAC-HZ-3P-2,0-542/ FR SCO BK - 1409537

### Accessories

Sealing cap - PROT-M12 FS-PA-CHAIN - 1430873

M12 sealing cap made of plastic with fixing band, for sensor cables, for free M12 plugs



---

### Safety locking

Locking clip - SAC-M12-EXCLIP-M - 1558988



Locking clip for the pin side of sensor/actuator cables with M12 connector and M12 connectors for assembly, for knurl diameter: 15 mm or for Allen key with a wrench size of 14 mm, prevents the disconnection of plug-in connections without tools

Locking clip - SAC-M12-EXCLIP-F - 1558991



Locking clip for the socket side of sensor/actuator cables with M12 connector and M12 connectors for assembly, for knurl diameter: 15 mm or for Allen key with a wrench size of 14 mm, prevents the disconnection of plug-in connections without tools

---

### Screwdriver tools

Adapter insert - TSD-M SAC-BIT ADAPTER - 1212600



Adapter bit for TSD-M...torque tools, E6.3-1/4" drive with 4 mm hexagon to accommodate SAC bits

Tool - SAC BIT M12-D15 - 1208432



Nut for assembling sensor/actuator cables with M12 connector and M12 connectors for assembly, with a knurl diameter of 15 mm, for 4 mm hexagonal drive

---

### Torque tool

## Sensor/actuator cable - SAC-HZ-3P-2,0-542/ FR SCO BK - 1409537

### Accessories

Torque screwdriver - TSD 04 SAC - 1208429



Torque screwdriver, with preset torque of 0.4 Nm and 4 mm hexagonal drive for M12 connectors

---

Torque screwdriver - TSD-M 1,2NM - 1212224



Torque screw driver, accuracy as per EN ISO 6789 standard, adjustable from 0.3 - 1.2 Nm

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

1409537