

FO connectors - FOC-C-SCDU-GOF-MM - 1411292

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



SC duplex connector, with long bend protection, for multi-mode 50/125 µm, beige

Product Description

SC duplex connector, for wires 2.0 mm ... 3.0 mm in diameter, multi-mode 50/125 µm. The reusable connector is particularly suitable for quick and easy field connection, as there is no need for bonding and polishing.

Your advantages

- ✓ suitable for quick and easy field assembly or repair
- ✓ No bonding or polishing
- ✓ Reusable connectors
- ✓ A real alternative to splicing
- ✓ Optimum attenuation values with easy assembly
- ✓ Long-term durability, thanks to the latest index matching gel
- ✓ the 8° fiber transition ensures optimum return loss (RL)
- ✓ meets IEC 61754-4 (SC) and FprEN 50377-17-1 (connectors for field assembly)
- ✓ Cleave technology
- ✓ Reusable connectors



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 924788
GTIN	4046356924788

Technical data

Mechanical characteristics

Connection method	mechanical splice
Cable outlet	straight
No. of cable outlets	1
Locking type	Clip locking

FO connectors - FOC-C-SCDU-GOF-MM - 1411292

Technical data

Mechanical characteristics

Weight	10 g
Flammability rating according to UL 94	V0

Ambient conditions

Ambient temperature (operation)	-10 °C ... 60 °C (IEC 61300-2)
Degree of protection	IP20

Electrical characteristics

Transmission speed	10 Gbps
--------------------	---------

Line characteristics

Type of cable	For all common cable types
Cable type	Fiberglass
Cable structure	Semi-loose compact wires (STB)
Number of fibers	1
Fiber type	Multi-mode fiberglass
Fiber	GOF
Attenuation	≤ 0.5 dB ((95%) according to IEC 61300-3-34)
	≤ 0.2 dB ((typical value) according to IEC 61300-3-34)
Tensile strength short-term/long-term	70N (120s.) bei Aderdurchmesser >2 mm
cable layer type	Indoors

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	19170122
eCl@ss 4.0	27260700
eCl@ss 4.1	27260700
eCl@ss 5.0	27260700
eCl@ss 5.1	27260700
eCl@ss 6.0	27180800
eCl@ss 8.0	19170122
eCl@ss 9.0	19170122

ETIM

ETIM 5.0	EC001122
ETIM 6.0	EC001122

FO connectors - FOC-C-SCDU-GOF-MM - 1411292

Classifications

ETIM

ETIM 7.0	EC001122
----------	----------

UNSPSC

UNSPSC 13.2	43223310
UNSPSC 18.0	43223310
UNSPSC 19.0	43223310
UNSPSC 20.0	43223310
UNSPSC 21.0	43223310

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		B.01742
-----	---	---------

Accessories

Accessories

Data cable by the meter

FO cable - FOC-OE-OE-GZ01/... - 1411561



Fiber optic cable, multi-mode fiberglass 50/125 µm, OM2, length: various

FO connectors - FOC-C-SCDU-GOF-MM - 1411292

Accessories

FO cable - FOC-OE-OE-GZ02/... - 1411563



Fiber optic cable, multi-mode fiber glass 50/125 µm, OM3, length: various

FO cable - FOC-OE-OE-GZ03/... - 1411564



Fiber optic cable, multi-mode fiberglass 50/125 µm, OM4, length: various

Data plug

FO accessories - FOC-TOOL-FERRULECLEANER-2.50 - 1407029



2.50 mm ferrule cleaner, for ST, SC, FC, E2000 (also APC), approx. 500 cleaning cycles

Tool set - FOC-TOOL-GOF KONF SET - 1411049



Tool set for GOF assembly

Necessary add-on products

Tool set - FOC-TOOL-GOF KONF SET - 1411049



Tool set for GOF assembly

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

1411292