

Patch cable - NBC-R4AC1/5,0-94G/R4AC1-YE - 1421173

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid
(<http://phoenixcontact.com/download>)



Patch cable, degree of protection: IP20, cable length: 5 m, number of positions: 8, 10 Gbps, CAT6A



Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4055626254845

Technical data

Cable type

Fixed cable length	5.00 m
Shielded	yes
Cable structure	2x2xAWG26/7; S-FTP
Conductor structure signal line	6.00 mm +0.2 mm -0.1 mm
AWG signal line	26
Shielding	S/FTP
Insulation resistance	2000 MΩ*km (500 V)
Coupling resistance	30.00 mΩ/m (30 MHz)
Test voltage	1000 V DC (1 minute)
Material wire insulation	PE

Ambient conditions

Ambient temperature (operation)	-25 °C ... 60 °C (RJ45 connector)
	-25 °C ... 75 °C (cable)

External sheath

Outer sheath, material	PUR
External sheath, color	yellow

Patch cable - NBC-R4AC1/5,0-94G/R4AC1-YE - 1421173

Technical data

General

Conductor length	5.00 m
Nominal voltage U _N	48 V
Transmission characteristics (category)	CAT6 _A
Transmission speed	10 Gbps
Degree of protection	IP20

Behavior in fire

Flame resistance	IEC 60332-1
------------------	-------------

Standards and Regulations

Flame resistance	IEC 60332-1
------------------	-------------


Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Drawings


Patch cable - NBC-R4AC1/5,0-94G/R4AC1-YE - 1421173

Schematic diagram



Connector pin assignment plug RJ45

Dimensional drawing



Patch cable - NBC-R4AC1/5,0-94G/R4AC1-YE - 1421173

Classifications

eCl@ss

eCl@ss 10.0.1	27060308
eCl@ss 7.0	27060308
eCl@ss 8.0	27060308
eCl@ss 9.0	27060308

ETIM

ETIM 6.0	EC001262
ETIM 7.0	EC001262

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		19060508
-----	---	----------

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phoenix Contact:

1421173