

## Mounting material - UM-BASIC/PRO PCB C-LOCK L3KMGY - 2202030

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Locking element for locking the PCB onto UM-BASIC/PRO housing at level 3

### Your advantages

- ✓ Different base profiles, each with three PCB levels
- ✓ Module covers of different geometries can be positioned in any way
- ✓ Compatibility with many standard connection technologies
- ✓ Easy device mounting thanks to snap-mount principle (the sides are fixed without the aid of tools)
- ✓ High degree of flexibility, thanks to freely positionable covering hoods

RoHS

### Key Commercial Data

Packing unit	50 pc
GTIN	 4 055626 005416
GTIN	4055626005416

### Technical data

#### Product properties

Brief article description	Mounting material
Type	UM-BASIC/PRO PCB C-LOCK L3KMGY
Order No.	2202030
Housing type	Press-drawn section housings
Mounting type	Plug-in mounting

#### Material specifications

Housing material	Polyamide
Color (RAL)	light gray (7035)
Flammability rating according to UL 94	V0

#### Ambient conditions

Ambient temperature (storage/transport)	-40 °C ... 55 °C
---	------------------

# Mounting material - UM-BASIC/PRO PCB C-LOCK L3KMGY - 2202030

## Technical data

### Ambient conditions

Ambient temperature (assembly)	-5 °C ... 100 °C
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Relative humidity (storage/transport)	80 %

### Mechanical strength/tumbling barrel

Specification	IEC 60068-2-31:2008-05
Height of fall	50 cm
Number of drop cycles	50

### Thermal stability (ball thrust test)

Specification	IEC 60695-10-2:2014-02
Temperature	125 °C
Test duration	1 h
Force	20

### Test for assessing the risk of fire (glow wire)

Specification	IEC 60695-2-11:2014-02
Temperature	850 °C
Time of exposure	30 s

### General information

Type of note	Assembly instruction:
Note	Refer to the data sheet for the range in the download area.

### Packaging specifications

Pieces per package	50
Denomination packing units	Pcs.

### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Classifications

### eCl@ss

eCl@ss 10.0.1	27182701
eCl@ss 5.0	27180500
eCl@ss 5.1	27180500
eCl@ss 6.0	27182000
eCl@ss 7.0	27182701
eCl@ss 8.0	27182701
eCl@ss 9.0	27182701

## Mounting material - UM-BASIC/PRO PCB C-LOCK L3KMGY - 2202030

### Classifications

#### ETIM

ETIM 5.0	EC002779
ETIM 6.0	EC002779
ETIM 7.0	EC002779

#### UNSPSC

UNSPSC 13.2	31261501
UNSPSC 18.0	31261501
UNSPSC 19.0	31261501
UNSPSC 20.0	31261501
UNSPSC 21.0	31261501

### Approvals

#### Approvals

---

#### Approvals

#### EAC

---

#### Ex Approvals

---

#### Approval details

EAC		B.01742
-----	---	---------

### Accessories

#### Accessories

#### Screwdriver tools

#### Screwdriver - SZF 0-0,4X2,5 - 1204504



Actuation tool, for ST terminal blocks, also suitable for use as a bladed screwdriver, size: 0.4 x 2.5 x 75 mm, 2-component grip, with non-slip grip

#### Necessary add-on products

## Mounting material - UM-BASIC/PRO PCB C-LOCK L3KMGY - 2202030

### Accessories

#### Profile - UM-BASIC PROFILE - 2200149



Press-drawn section housings, Basic profile, profile length (configurable): 3 cm ... 100 cm, color: light gray (7035),  
Note: required profile length = PCB length - 16.2 mm

---

#### Side element - UM-BASIC/PRO 72 COVER-L KMGY - 2202018



Lateral element (left) with mounting foot for DIN rails for UM-BASIC profiles with a PCB width of 72 mm

---

#### Side element - UM-BASIC/PRO 72 COVER-R KMGY - 2202019



Lateral element (right) with mounting foot for DIN rails for UM-BASIC profiles with a PCB width of 72 mm

---

#### Side element - UM-BASIC/PRO 108 COVER-L KMGY - 2202021



Lateral element (left) with mounting foot for DIN rails for UM-BASIC profiles with a PCB width of 108 mm

---

#### Side element - UM-BASIC/PRO 108 COVER-R KMGY - 2202022



Lateral element (right) with mounting foot for DIN rails for UM-BASIC profiles with a PCB width of 108 mm

## Mounting material - UM-BASIC/PRO PCB C-LOCK L3KMGY - 2202030

### Accessories

Side element - UM-BASIC/PRO 122 COVER-L KMGY - 2202045

Lateral element (left) with mounting foot for DIN rails for UM-BASIC profiles with a PCB width of 122 mm



Side element - UM-BASIC/PRO 122 COVER-R KMGY - 2202046

Lateral element (right) with mounting foot for DIN rails for UM-BASIC profiles with a PCB width of 122 mm



### Additional products

Functional ground contact - UM-BASIC/PRO PE CONTACT L1 - 2202025



PE contact for UM-BASIC panel mounting base for connecting the PCB to the DIN rail at level 1

Functional ground contact - UM-BASIC/PRO PE CONTACT L2 - 2202026



PE contact for UM-BASIC panel mounting base for connecting the PCB to the DIN rail at level 2

Functional ground contact - UM-BASIC/PRO PE CONTACT L3 - 2202027



PE contact for UM-BASIC panel mounting base for connecting the PCB to the DIN rail at level 3

## Mounting material - UM-BASIC/PRO PCB C-LOCK L3KMGY - 2202030

### Accessories

Mounting material - UM-BASIC/PRO PCB S-LOCK KMGY - 2202031



Locking element for locking the upper PCB onto UM-BASIC/PRO housings close to the edge

---

Mounting material - UM-BASIC/PRO PCB C-LOCK L1KMGY - 2202028



Locking element for locking the PCB onto UM-BASIC/PRO housing at level 1

---

Mounting material - UM-BASIC/PRO PCB C-LOCK L2KMGY - 2202029



Locking element for locking the PCB onto UM-BASIC/PRO housing at level 2

---

Mounting flange - UM-BASIC/PRO MOUNT KMGY - 2202032



Press-drawn section housings, Mounting flange for direct wall mounting, color: light gray (7035)

---

Foot element - UM-BASIC/PRO 72 FOOT KMGY - 2202020



Press-drawn section housings, for the DIN rail, for mounting below UM-BASIC PROFILE (width: 72 mm), Foot element, color: light gray (7035)

## Mounting material - UM-BASIC/PRO PCB C-LOCK L3KMGY - 2202030

### Accessories

#### Foot element - UM-BASIC/PRO 108 FOOT KMGY - 2202023

Press-drawn section housings, for the DIN rail, for mounting below UM-BASIC PROFILE (width: 108 mm), Foot element, color: light gray (7035)



#### Foot element - UM-BASIC/PRO 122 FOOT KMGY - 2202024

Press-drawn section housings, for the DIN rail, for mounting below UM-BASIC PROFILE (width: 122 mm), Foot element, color: light gray (7035)



#### Covering hood - UM-BASIC/PRO A/U N 73 CM - 2202035

Press-drawn section housings, Cover, width: 73 mm, profile length (configurable): 3 cm ... 100 cm, height: 24 mm, color: transparent, Note: max. length of the cover = PCB length = 19 mm



#### Covering hood - UM-BASIC/PRO A/U 73 CM - 2202036

Press-drawn section housings, Cover, width: 73 mm, profile length (configurable): 3 cm ... 100 cm, height: 63.2 mm, color: transparent, Note: max. length of the cover = PCB length = 19 mm



#### Covering hood - UM-BASIC/PRO A/U 92 CM - 2202037

Press-drawn section housings, Cover, width: 92 mm, profile length (configurable): 3 cm ... 100 cm, height: 34 mm, color: transparent, Note: max. length of the cover = PCB length = 19 mm



## Mounting material - UM-BASIC/PRO PCB C-LOCK L3KMGY - 2202030

### Accessories

#### Side element - UM-BASIC/PRO LID-73N KMGY - 2202034



Press-drawn section housings, Side element for low U-shaped profile cover, width: 10.35 mm, height: 78.43 mm, color: light gray (7035)

---

#### Side element - UM-BASIC/PRO LID-73 KMGY - 2202033



Press-drawn section housings, Side element for U-shaped profile cover, width: 10.35 mm, height: 78.49 mm, color: light gray (7035)

---

#### Side element - UM-BASIC/PRO LID-92 KMGY - 2202047



Press-drawn section housings, Side element for U-shaped profile cover, width: 10.35 mm, height: 97.51 mm, color: light gray (7035)

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2202030](#)