

## Insertion bridge - EB 3- DIK BU - 2716651

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Insertion bridge, pitch: 6.15 mm, number of positions: 3, color: blue

RoHS

### Key Commercial Data

|                        |                                                                                                         |
|------------------------|---------------------------------------------------------------------------------------------------------|
| Packing unit           | 10 pc                                                                                                   |
| Minimum order quantity | 10 pc                                                                                                   |
| GTIN                   | <br>4 017918 105082 |
| GTIN                   | 4017918105082                                                                                           |

### Technical data

#### Technical data

|                     |         |
|---------------------|---------|
| Color               | blue    |
| Material            | Copper  |
| Number of positions | 3       |
| Pitch               | 6.15 mm |

### Environmental Product Compliance

|            |                                                         |
|------------|---------------------------------------------------------|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
|            | No hazardous substances above threshold values          |

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 27141100 |
| eCl@ss 4.1 | 27141100 |
| eCl@ss 5.0 | 27141100 |
| eCl@ss 5.1 | 27141100 |
| eCl@ss 6.0 | 27141100 |

## Insertion bridge - EB 3- DIK BU - 2716651

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 7.0 | 27141140 |
| eCl@ss 8.0 | 27141140 |
| eCl@ss 9.0 | 27141140 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000489 |
| ETIM 3.0 | EC000489 |
| ETIM 4.0 | EC000489 |
| ETIM 5.0 | EC000489 |
| ETIM 6.0 | EC000489 |
| ETIM 7.0 | EC000489 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211829 |
| UNSPSC 7.0901 | 39121426 |
| UNSPSC 11     | 39121426 |
| UNSPSC 12.01  | 39121426 |
| UNSPSC 13.2   | 39121426 |
| UNSPSC 19.0   | 39121426 |

### Approvals

#### Approvals

#### Approvals

#### EAC

#### Ex Approvals

#### Approval details

|     |                                                                                     |                          |
|-----|-------------------------------------------------------------------------------------|--------------------------|
| EAC |  | RU C-<br>DE.A*30.B.01742 |
|-----|-------------------------------------------------------------------------------------|--------------------------|

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2716651](#)