


Interface module - UM-RJ45/RJ11/MKDS - 2306197

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

VARIOFACE module, with screw connection and two RJ45 sockets, for mounting on NS 32 or NS 35/7.5

RoHS

Key Commercial Data

Packing unit	5 pc
Minimum order quantity	30 pc
GTIN	 4 017918 961695
GTIN	4017918961695

Technical data

Dimensions

Width	23 mm
Height	90 mm
Depth	52 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
---------------------------------	------------------

General

Max. perm. operating voltage	< 50 V AC/DC
Max. perm. current (per branch)	1 A
Mounting position	any
Degree of protection	IP20

Connection data for connection 1

Connection name	RJ45 connection
Number of connections	2
Number of positions	8

Connection data for connection 2

Connection name	COMBICON connection
Connection method	Screw connection
Conductor cross section solid	0.14 mm ² ... 1.5 mm ²
Conductor cross section flexible	0.14 mm ² ... 1.5 mm ²
Conductor cross section AWG	26 ... 16

Interface module - UM-RJ45/RJ11/MKDS - 2306197

Technical data

Connection data for connection 2

Number of positions	4
---------------------	---

Standards and Regulations

Designation	Air clearances and creepage distances
Standards/regulations	DIN EN 50178: 1998-04
Rated insulation voltage	63 V
Rated surge voltage	0.6 kV (1.2/50 µs)
Insulation	Functional insulation
Degree of pollution	2
Overvoltage category	II

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU C- DE.A*30.B.01742
-----	---	--------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2306197](#)