

Network cable - NBC-M12MSD/2,37-93B CV - 1036682

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Network cable, PROFINET CAT5, 4-position, PVC/PVC, green RAL 6018, shielded, Plug straight M12 / IP67, coding: D, on free cable end, cable length: 2.37 m, Pre-construction stage

RoHS

Key Commercial Data

Packing unit	1 pc
Minimum order quantity	50 pc
GTIN	 4 055626 569338
GTIN	4055626569338

Technical data

Dimensions

Length of cable	2.37 m
-----------------	--------

General data

Number of positions	4
Signal type/category	PROFINET CAT5 (IEC 11801)
Transmission characteristics (category)	CAT5

Characteristics head 1

Head type	Plug straight M12 / IP67
Coding	D
Outer sheath, material	PVC
External sheath, color	green RAL 6018

Characteristics head 2

Head type	free cable end
-----------	----------------

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	27060308
---------------	----------

Network cable - NBC-M12MSD/2,37-93B CV - 1036682

Classifications

eCl@ss

eCl@ss 9.0	27060308
------------	----------

ETIM

ETIM 6.0	EC001262
ETIM 7.0	EC001262

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1036682](#)