

## End cover - D-PTV 2,5/4-QUATTRO - 1088748

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

End cover, length: 69.2 mm, width: 2.2 mm, height: 45.7 mm, color: gray



RoHS

### Key Commercial Data

|                        |                                                                                                         |
|------------------------|---------------------------------------------------------------------------------------------------------|
| Packing unit           | 50 pc                                                                                                   |
| Minimum order quantity | 50 pc                                                                                                   |
| GTIN                   | <br>4 055626 890173 |
| GTIN                   | 4055626890173                                                                                           |

### Technical data

#### General

|                                        |      |
|----------------------------------------|------|
| Color                                  | gray |
| Material                               | PA   |
| Flammability rating according to UL 94 | V0   |

#### Dimensions

|        |         |
|--------|---------|
| Width  | 2.2 mm  |
| Length | 69.2 mm |
| Height | 45.7 mm |

#### General

|                                          |                                                                        |
|------------------------------------------|------------------------------------------------------------------------|
| Ambient temperature (operation)          | -60 °C ... 85 °C                                                       |
| Ambient temperature (storage/transport)  | -25 °C ... 55 °C (For a short time, not exceeding 24 h, -60 to +70 °C) |
| Permissible humidity (storage/transport) | 30 % ... 70 %                                                          |
| Ambient temperature (assembly)           | -5 °C ... 70 °C                                                        |
| Ambient temperature (actuation)          | -5 °C ... 70 °C                                                        |

### Standards and Regulations

|                                        |    |
|----------------------------------------|----|
| Flammability rating according to UL 94 | V0 |
|----------------------------------------|----|

## End cover - D-PTV 2,5/4-QUATTRO - 1088748

### Classifications

#### eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27141133 |
| eCl@ss 4.0    | 27141111 |
| eCl@ss 4.1    | 27141111 |
| eCl@ss 5.0    | 27141133 |
| eCl@ss 5.1    | 27141100 |
| eCl@ss 6.0    | 27141100 |
| eCl@ss 7.0    | 27141133 |
| eCl@ss 8.0    | 27141133 |
| eCl@ss 9.0    | 27141133 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000886 |
| ETIM 3.0 | EC000886 |
| ETIM 4.0 | EC000886 |
| ETIM 5.0 | EC000886 |
| ETIM 6.0 | EC000886 |
| ETIM 7.0 | EC000886 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211827 |
| UNSPSC 7.0901 | 39121424 |
| UNSPSC 11     | 39121424 |
| UNSPSC 12.01  | 39121424 |
| UNSPSC 13.2   | 39121425 |
| UNSPSC 18.0   | 39121425 |
| UNSPSC 19.0   | 39121425 |
| UNSPSC 20.0   | 39121425 |
| UNSPSC 21.0   | 39121425 |

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1088748](#)