

## Patch panels - FOC-FR19:1U-2OS12-LCD12-OM1 - 1419973

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




### Your advantages

- ✓ Fast and reliable cabling, thanks to clear connections on the front
- ✓ Plug & Play
- ✓ Compact design with MT ferrule



### Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 198903
GTIN	4055626198903

### Technical data

#### Mechanical characteristics

Number of slots	12
No. of cable outlets	0
Locking type	Push Pull
Weight	1770 g
Type	19" rack patch module
Flammability rating according to UL 94	V0

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C (IEC 61300-2-22)
Degree of protection	IP20
	IP20

#### Material data

Housing material	Aluminum alloy
------------------	----------------

## Patch panels - FOC-FR19:1U-2OS12-LCD12-OM1 - 1419973

### Technical data

#### Material data

Housing surface material	Powder-coated, gray
Width	482.6 mm
Height	132 mm
Depth	220 mm
Mounting type	Screw mounting

#### Standards and Regulations

Halogen-free	complying with IEC 60754-1/2
Flammability rating according to UL 94	V0

#### Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

### Classifications

#### eCl@ss

eCl@ss 10.0.1	27440219
eCl@ss 8.0	27440102
eCl@ss 9.0	27440219

### Accessories

#### Additional products

Connecting cable - FOC-OP12-OP12-GL02/10 - 1415353



Double-end preassembled cable, type: circular connector, degree of protection: IP68, number of positions: 12

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1419973](#)