

End cover - HC-ALU 6-78 COVER GY - 2200896

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Profile housing, Side part, length: 15 mm, width: 101.9 mm

Your advantages

- ✓ Item is from the HC-ALU product range
- ✓ Aluminum press-drawn section
- ✓ Available in lengths from 100 mm ... 1000 mm, can be individually cut to any length
- ✓ Available in overall widths 53.5 mm ... 161 mm
- ✓ Degree of protection up to IP65
- ✓ Usable as handheld and wall housing
- ✓ Optional EMC seals available

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 716772
GTIN	4046356716772

Technical data

General

Housing type	Profile housing
--------------	-----------------

Dimensions

Length	15 mm
Installed height	36.2 mm
Width	101.9 mm
Depth	78 mm

End cover - HC-ALU 6-78 COVER GY - 2200896

Classifications

eCl@ss

eCl@ss 10.0.1	27182701
eCl@ss 4.0	27180400
eCl@ss 4.1	27180400
eCl@ss 5.0	27180500
eCl@ss 5.1	27180500
eCl@ss 6.0	27182000
eCl@ss 7.0	27182701
eCl@ss 8.0	27182701
eCl@ss 9.0	27182701

ETIM

ETIM 3.0	EC001031
ETIM 4.0	EC000721
ETIM 5.0	EC002779
ETIM 6.0	EC002779
ETIM 7.0	EC002779

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501
UNSPSC 18.0	31261501
UNSPSC 19.0	31261501
UNSPSC 20.0	31261501
UNSPSC 21.0	31261501

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

End cover - HC-ALU 6-78 COVER GY - 2200896

Approvals

EAC



B.01742

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2200896](#)