

Side element - UM-ALU 4-100,5 COVERLID 75 AL - 2201760

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Press-drawn section housings, Side elements (left and right) incl. snap-on foot and screws for profile cover UM-ALU 4 AU..L..., width: 105.4 mm, height: 2 mm, color: aluminum color



Your advantages

- ✓ Item is from the UM-ALU product range
- ✓ Aluminum press-drawn section
- ✓ Available in lengths from 42.5 mm ... 990 mm, can be cut to any length
- ✓ Available in overall widths of 75 mm and 105 mm
- ✓ Variety of connection technologies
- ✓ Can be mounted on the DIN rail
- ✓ EMC protection

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 909068
GTIN	4046356909068

Technical data

Product properties

Brief article description	Side element
Type	UM-ALU 4-100,5 COVERLID 75 AL
Order No.	2201760
Housing type	Press-drawn section housings
Type	Side elements (left and right) incl. snap-on foot and screws for profile cover UM-ALU 4 AU..L..
Max. IP code to attain	IP40
Mounting type	Screw mounting

Dimensions

Side element - UM-ALU 4-100,5 COVERLID 75 AL - 2201760

Technical data

Dimensions

Width [w]	105.4 mm
Height [h]	2 mm
Depth [d]	73.5 mm

Material specifications

Material	Aluminum
Color	aluminum color
Surface characteristics	anodized

Ambient conditions

Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)

Note on mounting

Tightening torque / rotational speed	Screw connection with header/profile cover: 0.8 Nm-1 Nm / rpm- rpm
--------------------------------------	--

Packaging specifications

Type of packaging	packed in cardboard
Pieces per package	1
Denomination packing units	Pcs.
Outer packaging type	Carton

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	27182701
eCl@ss 5.0	27180500
eCl@ss 5.1	27180500
eCl@ss 6.0	27182000
eCl@ss 7.0	27182701
eCl@ss 8.0	27182701
eCl@ss 9.0	27182701

ETIM

ETIM 4.0	EC001031
ETIM 5.0	EC002779
ETIM 6.0	EC002779
ETIM 7.0	EC002779

Side element - UM-ALU 4-100,5 COVERLID 75 AL - 2201760

Classifications

UNSPSC

UNSPSC 13.2	31261501
UNSPSC 18.0	31261501
UNSPSC 19.0	31261501
UNSPSC 20.0	31261501
UNSPSC 21.0	31261501

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		B.01742
-----	---	---------

Accessories

Accessories

Component housing cover

Profile cover - UM-ALU 4 AU75 L42,5 - 2200963



Press-drawn section housings, Profile cover, width: 75.6 mm, profile width (internal): 71.5 mm, length: 42.5 mm, color: aluminum color

Profile cover - UM-ALU 4 AU75 L60 - 2200964



Press-drawn section housings, Profile cover, width: 75.6 mm, profile width (internal): 71.5 mm, length: 60 mm, color: aluminum color

Side element - UM-ALU 4-100,5 COVERLID 75 AL - 2201760

Accessories

Profile cover - UM-ALU 4 AU75 L95 - 2200965



Press-drawn section housings, Profile cover, width: 75.6 mm, profile width (internal): 71.5 mm, length: 95 mm, color: aluminum color

Profile cover - UM-ALU 4 AU75 L130 - 2200966



Press-drawn section housings, Profile cover, width: 75.6 mm, profile width (internal): 71.5 mm, length: 130 mm, color: aluminum color

Profile cover - UM-ALU 4 AU75 L165 - 2200967



Press-drawn section housings, Profile cover, width: 75.6 mm, profile width (internal): 71.5 mm, length: 165 mm, color: aluminum color

Profile cover - UM-ALU 4 AU75 L200 - 2200968



Press-drawn section housings, Profile cover, width: 75.6 mm, profile width (internal): 71.5 mm, length: 200 mm, color: aluminum color

Profile cover - UM-ALU 4 AU75 L235 - 2200969



Press-drawn section housings, Profile cover, width: 75.6 mm, profile width (internal): 71.5 mm, length: 235 mm, color: aluminum color

Side element - UM-ALU 4-100,5 COVERLID 75 AL - 2201760

Accessories

Profile cover - UM-ALU 4 AU75 L990 - 2200970



Press-drawn section housings, Profile cover, width: 75.6 mm, profile width (internal): 71.5 mm, length: 990 mm, color: aluminum color

Component housing lower part

Profile - UM-ALU 4-100,5 PROFILE 42,5 - 2200935



Press-drawn section housings, Basic profile, profile width (internal): 100.5 mm, length: 42.5 mm, color: aluminum color

Profile - UM-ALU 4-100,5 PROFILE 60 - 2200936



Press-drawn section housings, Basic profile, profile width (internal): 100.5 mm, length: 60 mm, color: aluminum color

Profile - UM-ALU 4-100,5 PROFILE 95 - 2200937



Press-drawn section housings, Basic profile, profile width (internal): 100.5 mm, length: 95 mm, color: aluminum color

Profile - UM-ALU 4-100,5 PROFILE 130 - 2200938



Press-drawn section housings, Basic profile, profile width (internal): 100.5 mm, length: 130 mm, color: aluminum color

Side element - UM-ALU 4-100,5 COVERLID 75 AL - 2201760

Accessories

Profile - UM-ALU 4-100,5 PROFILE 165 - 2200939



Press-drawn section housings, Basic profile, profile width (internal): 100.5 mm, length: 165 mm, color: aluminum color

Profile - UM-ALU 4-100,5 PROFILE 200 - 2200940



Press-drawn section housings, Basic profile, profile width (internal): 100.5 mm, length: 200 mm, color: aluminum color

Profile - UM-ALU 4-100,5 PROFILE 235 - 2200941



Press-drawn section housings, Basic profile, profile width (internal): 100.5 mm, length: 235 mm, color: aluminum color

Profile - UM-ALU 4-100,5 PROFILE 990 - 2200942



Press-drawn section housings, Basic profile, profile width (internal): 100.5 mm, length: 990 mm, color: aluminum color

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2201760](#)